

インチネジ

Inch Screw

2015 NEW Model 新製品

ねじり破断トルク

Torsional rupture torque

単位/Unit	4-40	6-32	8-32	10-32	1/4-20
N・m	0.17	0.34	0.62	1.06	1.87

引張破断荷重

Tensile rupture force

単位/Unit	4-40	6-32	8-32	10-32	1/4-20
N	288	431	703	1064	1648

外観に黒点(スラッジ)が入ることがありますが性能には影響ありません。

ネジ先端部のゲート残りは0.2mm以下です。

- ・表中の数値は参考値であり保証値ではありません。
- ・締付にはトルクドライバー及びトルクレンチをご使用ください。推奨締付トルクは使用状態においての破断トルク値の50%です。
- ・耐熱性、耐薬品性は使用条件により変化しますので、必ず事前に使用状態でのテストを行ってください。
- ・ロット、各種条件により若干変色することがあります。
- ・在庫サイズ、形状及び使用材料メーカーは予告なく変更することがあります。

Black spots may occasionally appear on the external surface. However, this has no impact on performance.

Gate residue of screw head is 0.2mm or less.

- ・ Values in the table are for reference purpose only, and they are not guaranteed values.
- ・ Please use torque driver or torque wrench for fastening. Recommended fastening torque is 50% of the torsional rupture torque.
- ・ Since heat resistance and chemical resistance change based on usage conditions, please test under actual usage conditions beforehand.
- ・ Discoloration may occur depending on lot and various conditions.
- ・ Sizes, shapes and manufacturers of raw materials may change without notice.

PEEK

Polyether ether ketone

ポリエーテルエーテルケトン

連続使用温度

Continuous use temperature

180°C/356°F

燃焼性

UL94 V-0


Flammability : UL94 V-0

PEEK/PH



Inch Screw

ポリエーテルエーテルケトン / (+)ナベ小ネジ
Polyether ether ketone / Cross recessed pan head screw



Thread size

品番 Product number PEEK/PH (Thread size) - L

ネジ径/ Thread size	4-40	6-32	8-32	10-32	1/4-20
D × H (inch)	0.219 × 0.080	0.270 × 0.097	0.322 × 0.115	0.373 × 0.133	0.492 × 0.175
L	1/4	100	100	100	—
	5/16	100	100	100	—
	3/8	100	100	100	100
	1/2	100	100	100	100
	5/8	100	100	100	100
	3/4	100	100	100	100
	7/8	100	100	100	100
	1	100	100	100	100
1-1/4	—	—	—	—	100


販売単位 Quantity

PEEK/(-)PH



Inch Screw

ポリエーテルエーテルケトン / (-)ナベ小ネジ
Polyether ether ketone / Slotted pan head screw



Thread size

品番 Product number PEEK/(-)PH (Thread size) - L

ネジ径/ Thread size	4-40	6-32	8-32	10-32
D (inch)	0.219 × 0.068	0.270 × 0.082	0.322 × 0.096	0.373 × 0.110
y (inch)	0.039	0.048	0.054	0.060
c (inch)	0.040	0.050	0.058	0.068
L	1/4	100	100	—
	5/16	100	100	—
	3/8	100	100	100
	1/2	100	100	100
	5/8	100	100	100
	3/4	100	100	100
	7/8	100	100	100
	1	100	100	100

販売単位 Quantity

新製品
PC
PPS
RENY
PEEK
PVC
PI
PP
PTFE
PFA
PVDF
CERAMIC
PA
POM
PO/PS
フッ素樹脂
オキシソ
サービ
材質・
技術資料