

TOMBO No.9002

ナフロン®PTFEロッド(1000mm)

標準寸法

単位：(mm)

直 径		長 さ	
寸 法	許容差	最大寸法	許容差
1.0	+0.4 － 0	1000	+ 20 － 0
2.0			
3.0			
4.0			
5.0			
6.0			
★ 6.2			
7.0			
7.3			
7.5			
8.0			
9.0			
10.0			
★ 10.3			
11.0			+0.6 － 0
12.0	+0.7 － 0		
★ 12.3			
13.0			
14.0			
15.0			
16.0			
17.0			
18.0			
20.0	+1.0 － 0		
22.0			
25.0			
30.0	+1.5 － 0		
35.0			
40.0			
45.0			
50.0	+3.0 － 0		
55.0	+4.0 － 0		
60.0			
65.0			
70.0			
80.0	+5.0 － 0		
90.0			
100.0			
120.0	+6.0 － 0		
150.0	+7.0 － 0		

※ ★印は受注生産品となります。

TOMBO No.9002

ナフロン®PTFEロッド(100mm)

標準寸法

単位：(mm)

直 径		長さ (標準寸法100mm)	
寸 法	許容差	最大寸法	許容差
15	+2.0 — 0	150	+4.0 — 0
17			
18			
20			
22			
23			
25			
27			
28			
30			
33			
35			
38			
40			
43			
45	+4.0 — 0	250	+5.0 — 0
46			
50			
55			
60			
65			
70			
75			
80			
85			
90			
95			
100			
105			
110			
115			
120			
130			
135			
140			
150			
160			
170			
180			
190			
200			
210			
220			

※ 直径、長さについては、上記以外の寸法も製作可能ですのでご相談ください。