

MHRLN230-6


Size $\phi 0.3 \sim \phi 2$



MUGEN COATING 2-Flute Long Neck End Mill (Shank Dia. 6)

Total 19 sizes

2-flute long neck square end mill. Shank Dia.6mm



- Carbon Steel **P**
- Alloy Steel **P**
- Prehardened Steel **P**
- Hardened Steel ~ 55 HRC **H**

Stainless Steel **M**

Aluminium Alloy **N**

Copper **N**

Resin **O**

Long Neck Square Coating

Unit : mm

Code No.	Dia. (D)	Under Neck Length (ℓ_1)	Length of Cut (ℓ)	Neck Dia. (d2)	Neck Taper Angle (γ)	Shank Dia. (d)	Overall Length (L)
08-00202-03030	0.3	3	0.4	0.28	15°	6	60
08-00202-04030		3	0.6	0.37	15°	6	60
08-00202-04040	0.4	4	0.6	0.37	15°	6	60
08-00202-04050		5	0.6	0.37	15°	6	60
08-00202-05040	0.5	4	0.7	0.46	15°	6	60
08-00202-05050		5	0.7	0.46	15°	6	60
08-00202-05060		6	0.7	0.46	15°	6	60
08-00202-06040	0.6	4	0.9	0.56	15°	6	60
08-00202-06060		6	0.9	0.56	15°	6	60
08-00202-08080	0.8	8	1.2	0.76	15°	6	60
08-00202-10030	1	3	1.5	0.95	15°	6	60
08-00202-10060		6	1.5	0.95	15°	6	60
08-00202-10080		8	1.5	0.95	15°	6	60
08-00202-10100		10	1.5	0.95	15°	6	60
08-00202-15030	1.5	3	2.3	1.45	15°	6	60
08-00202-15050		5	2.3	1.45	15°	6	60
08-00202-15100		10	2.3	1.45	15°	6	60
08-00202-15150		15	2.3	1.45	15°	6	60
08-00202-20200	2	20	3	1.94	15°	6	60

How to Order When you order, indicate MHRLN230-6 (D) \times (ℓ_1). ※(γ) is reference value.

■ Semi-standard products, please inquire for price and delivery.