

輕荷重
경하중
LIGHT LOAD



하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load

SL 8×10	8	4	10	2.50	4.0	10	3.6	9	3.2	8
15			15	1.67	6.0		5.4		4.8	
20			20	1.25	8.0		7.2		6.4	
25			25	1.00	10.0		9.0		8.0	
30			30	0.83	12.0		10.8		9.6	
35			35	0.71	14.0		12.6		11.2	
40			40	0.63	16.0		14.4		12.8	
45			45	0.56	18.0		16.2		14.4	
50			50	0.50	20.0		18.0		16.0	
55			55	0.46	22.0		19.8		17.6	
60			60	0.42	24.0		21.6		19.2	
65			65	0.38	26.0		23.4		20.8	
70			70	0.36	28.0		25.2		22.4	
75			75	0.33	30.0		27.0		24.0	
80			80	0.31	32.0		28.8		25.6	
90			90	0.28	36.0		32.4		28.8	
SL 10×10	10	5	10	3.61	4.0	14.5	3.6	13	3.2	11.5
15			15	2.41	6.0		5.4		4.8	
20			20	1.81	8.0		7.2		6.4	
25			25	1.45	10.0		9.0		8.0	
30			30	1.21	12.0		10.8		9.6	
35			35	1.03	14.0		12.6		11.2	
40			40	0.90	16.0		14.4		12.8	
45			45	0.80	18.0		16.2		14.4	
50			50	0.73	20.0		18.0		16.0	
55			55	0.66	22.0		19.8		17.6	
60			60	0.60	24.0		21.6		19.2	
65			65	0.55	26.0		23.4		20.8	
70			70	0.51	28.0		25.2		22.4	
75			75	0.48	30.0		27.0		24.0	
80			80	0.45	32.0		28.8		25.6	
90			90	0.40	36.0		32.4		28.8	
100	100	0.36	40.0	36.0	32.0					