

パイプ、溶接配管用継手



Pipes, Fitting for Welding end

溶接式レジュース／溶接式偏心レジュース
Reducer (Concentric) both end Weld / Reducer (Eccentric) both end Weld

溶接式レジュース

Reducer (Concentric) both end Weld

Type RDC-W





※寸法は下表に同じ
Size is same to the below chart

溶接式偏心レジュース

Reducer (Eccentric) both end Weld

Type RDE-W



Nom.size	OD1	OD2	t1	t2	L	Mass kg
1.25 ^S × 1.0 ^S	31.8	25.4	1.2	1.2	67	0.06
1.5 ^S × 1.25 ^S	38.1	31.8	1.2	1.2	67	0.08
1.5 ^S × 1.0 ^S	38.1	25.4	1.2	1.2	67	0.07
2.0 ^S × 1.5 ^S	50.8	38.1	1.5	1.2	67	0.11
2.0 ^S × 1.25 ^S	50.8	31.8	1.5	1.2	67	0.10
2.0 ^S × 1.0 ^S	50.8	25.4	1.5	1.2	67	0.10
2.5 ^S × 2.0 ^S	63.5	50.8	2	1.5	67	0.19
2.5 ^S × 1.5 ^S	63.5	38.1	2	1.2	67	0.14
2.5 ^S × 1.25 ^S	63.5	31.8	2	1.2	67	0.19
2.5 ^S × 1.0 ^S	63.5	25.4	2	1.2	67	0.17
3.0 ^S × 2.5 ^S	76.3	63.5	2	2	67	0.21
3.0 ^S × 2.0 ^S	76.3	50.8	2	1.5	67	0.17
3.0 ^S × 1.5 ^S	76.3	38.1	2	1.2	67	0.22
3.5 ^S × 3.0 ^S	89.1	76.3	2	2	67	0.23
3.5 ^S × 2.5 ^S	89.1	63.5	2	2	67	0.24
3.5 ^S × 2.0 ^S	89.1	50.8	2	1.5	67	0.28
4.0 ^S × 3.5 ^S	101.6	89.1	2	2	102	0.39
4.0 ^S × 3.0 ^S	101.6	76.3	2	2	102	0.46
4.0 ^S × 2.5 ^S	101.6	63.5	2	2	102	0.60
4.0 ^S × 2.0 ^S	101.6	50.8	2	1.5	102	0.49
※ 10A × 8A	17.3	13.8	1.65	1.65	38.1	
※ 15A × 8A	21.7	13.8	2.1	1.65	38.1	0.032
※ 15A × 10A	21.7	17.3	2.1	1.65	38.1	0.033
※ 1.0 ^S × 8A	25.4	13.8	1.2	1.65	38.1	0.028
※ 1.0 ^S × 10A	25.4	17.3	1.2	1.65	38.1	0.031
※ 1.0 ^S × 15A	25.4	21.7	1.2	2.1	38.1	0.037
※ 1.5 ^S × 8A	38.1	13.8	1.2	1.65	38.1	0.041
※ 1.5 ^S × 10A	38.1	17.3	1.2	1.65	38.1	0.043
※ 1.5 ^S × 15A	38.1	21.7	1.2	2.1	38.1	0.047

※SUS316Lのみ
Only SUS316L

写真は3DCGです。