



## MCD (for Stainless steel twin wheeled compact heavy duty castors)

- Tire Conductive monomer cast nylon (Black)
  - Wheel center -
  - Bearing **SJBB** Stainless steel radial ball bearing
  - Operating temp. -40°C~+120°C (temporarily ~+150°C)
  - Hardness (R) 115-120
  - Volume resistance  $10^2 \sim 10^4 \Omega \cdot \text{cm}^*$
  - Characteristics Chemical, oil and wearing resistance.
  - Applicable to Castors on P.11 P.45
- \*For reference only, not guaranteed.



MCD-50HWTU <b>SJBB</b>	50	15×2	36	8	300 (2940)
MCD-65HWTU <b>SJBB</b>	65	17×2	40	10	400 (3920)
MCD-75HWTU <b>SJBB</b>	75	18.5×2	43	10	500 (4900)

## MCDG (for Compact heavy duty castors)

- Tire Conductive nylon (Gray)
  - Wheel center -
  - Bearing **NB** Needle bearing
  - Operating temp. -40°C~+120°C
  - Hardness (R) 115-120
  - Volume resistance  $10^2 \Omega \cdot \text{cm}^*$
  - Characteristics Oil and chemical resistance. Floor saving.
  - Applicable to Castors on P.39
- \*For reference only, not guaranteed.



MCDG-50**	50	32.5	36	8	120 (1170)
MCDG-65 <b>NB</b>	65	36	40	10	260 (2540)
MCDG-75 <b>NB</b>	75	39	43	10	300 (2940)

\*\*MCDG-50: without bearing.

## MCMO (for Compact heavy duty castors)

- Tire Monomer cast nylon
- Wheel center -
- Bearing **JBB** Radial ball bearing
- Operating temp. -40°C~+120°C (temporarily ~+150°C)
- Hardness (R) 115-120
- Characteristics Chemical, oil and wearing resistance.
- Applicable to Castors on P.19 P.23 (80-100HW)



MCMO-50HW <b>JBB</b>	50	32.5	35.5	8	300 (2940)
MCMO-65HW <b>JBB</b>	65	36	39	10	400 (3920)
MCMO-75HW <b>JBB</b>	75	39	42	10	500 (4900)
MCMO-80HW* <b>JBB</b>	80	40	43	12	1000 (9800)
MCMO-100HW* <b>JBB</b>	100	40	43	12	1000 (9800)

\*MCMO-80/100HW: with steel bushing  
\*MCMO-80/100HW: for DHJ/DHK series. (p.23)

MCMO-80HW\*

## MCMO (for Stainless steel compact heavy duty castors)

- Tire Monomer cast nylon
- Wheel center -
- Bearing **SJBB** Stainless steel radial ball bearing
- Operating temp. -40°C~+120°C (temporarily ~+150°C)
- Hardness (R) 115-120
- Characteristics Chemical, oil and wearing resistance.
- Applicable to Castors on P.43



MCMO-50HWSU <b>SJBB</b>	50	32.5	35.5	8	300 (2940)
MCMO-65HWSU <b>SJBB</b>	65	36	39	10	400 (3920)
MCMO-75HWSU <b>SJBB</b>	75	39	42	10	500 (4900)

## MCMO (for Twin wheeled compact heavy duty castors)

- Tire Monomer cast nylon
- Wheel center -
- Bearing **JBB** Radial ball bearing
- Operating temp. -40°C~+120°C (temporarily ~+150°C)
- Hardness (R) 115-120
- Characteristics Chemical, oil and wearing resistance.
- Applicable to Castors on P.9 P.21



MCMO-50HWT <b>JBB</b>	50	15×2	36	8	300 (2940)
MCMO-65HWT <b>JBB</b>	65	17×2	40	10	400 (3920)
MCMO-75HWT <b>JBB</b>	75	18.5×2	43	10	500 (4900)

## MCMO (for Stainless steel twin wheeled compact heavy duty castors)

- Tire Monomer cast nylon
- Wheel center -
- Bearing **SJBB** Stainless steel radial ball bearing
- Operating temp. -40°C~+120°C (temporarily ~+150°C)
- Hardness (R) 115-120
- Characteristics Chemical, oil and wearing resistance.
- Applicable to Castors on P.11 P.45



MCMO-50HWTU <b>SJBB</b>	50	15×2	36	8	300 (2940)
MCMO-65HWTU <b>SJBB</b>	65	17×2	40	10	400 (3920)
MCMO-75HWTU <b>SJBB</b>	75	18.5×2	43	10	500 (4900)