



## SUW (for Stainless steel castors)

- Tire UR (Polyurethane)
- Wheel center SUS 304
- Bearing **NBS** Stainless steel needle bearing
- Operating temp. SUW-75: -15°C~+80°C  
SUW-100~150: -30°C~+80°C
- Hardness (HS) 90-92
- Characteristics Shock, oil and acid resistance.
- Applicable to Castors on P.41



SUW-75*	75	25	31	8	—	70 (680)
SUW-100 <b>NBS</b>	100	35	42	10	10.0	150 (1470)
SUW-125 <b>NBS</b>	125	42	56	12	11.5	210 (2050)
SUW-150 <b>NBS</b>	150	45	56	12	12.0	250 (2450)

\*SUW-75: with nylon bushing. (w/o bearing)



SUW-75\*

## SW (for Stainless steel castors)

- Tire SBR
- Wheel center SUS 304
- Bearing **NBS** Stainless steel needle bearing
- Operating temp. SW-75: -40°C~+80°C  
SW-100~150: -30°C~+90°C
- Hardness (HS) 70-75
- Characteristics Wearing resistance. High elasticity.
- Applicable to Castors on P.41



SW-75*	75	25	30	8	—	60 (580)
SW-100 <b>NBS</b>	100	35	42	10	10.0	150 (1470)
SW-125 <b>NBS</b>	125	42	56	12	11.5	210 (2050)
SW-150 <b>NBS</b>	150	45	56	12	12.0	250 (2450)

\*SW-75: with nylon bushing. (w/o bearing)



SW-75\*

## SWUW (for Stainless steel castors)

- Tire UR (Antibacterial white polyurethane)
- Wheel center SUS 304
- Bearing **NBS** Stainless steel needle bearing
- Operating temp. -30°C~+80°C
- Hardness (HS) 75
- Characteristics Antibacterial effect. High elasticity. Oil resistance.
- Applicable to Castors on P.41



SWUW-100 <b>NBS</b>	100	35	42	10	10.0	150 (1470)
SWUW-125 <b>NBS</b>	125	42	56	12	11.5	210 (2050)
SWUW-150 <b>NBS</b>	150	45	56	12	12.0	250 (2450)

## TRAW

- Tire Highly durable rubber
- Wheel center Die-cast aluminum
- Bearing **JBB** Radial ball bearing
- Operating temp. -30°C~+90°C
- Hardness (HS) 60
- Characteristics High elasticity. Low starting resistance.
- Applicable to Castors on P.27 P.31



TRAW-200 <b>JBB</b>	200	45	55	20	21.5	250 (2450)
---------------------	-----	----	----	----	------	---------------

## U (for Compact heavy duty castors)

- Tire UR (Polyurethane)
- Wheel center A2017BD-T
- Bearing **JBB** Radial ball bearing
- Operating temp. -30°C~+80°C
- Hardness (HS) 90-92
- Characteristics Shock and oil resistance.
- Applicable to Castors on P.19



U-35HW* <b>JBB</b>	35	27	30	6	4.5	100 (980)
U-50HW <b>JBB</b>	50	32.5	35.5	8	6.0	240 (2350)
U-65HW <b>JBB</b>	65	36	39	10	6.5	320 (3130)
U-75HW <b>JBB</b>	75	39	42	10	7.5	400 (3920)

\*U-35HW: with steel bushing.

## U (for Corner castors)

- Tire UR (Polyurethane)
- Wheel center —
- Bearing —
- Operating temp. -15°C~+80°C
- Hardness (HS) 90-92
- Characteristics Shock and oil resistance.
- Applicable to Castors on P.47



U-50CC	50	20	23	6	—	35 (340)
U-65CC	65	25	31	8	—	50 (490)
U-75CC	75	25	31	8	—	60 (580)