


CoroMill® 365 face milling cutter

Arbor

Wedge clamp design

STDNO
KAPR

ISO 6462:2011
65°



Metric version

DC CZC _{MS} APMX CNSC Ordering code						Dimensions							CICT MID	
DC	ISO	DBC	DCX	LF	Nm	Kg	RPMX	CICT	MID					
80.0	A		86.7	50.0	6.0	1.45	11200	10	R365-1505ZNE					
100.0	A		106.7	50.0	6.0	2.00	9900	14	R365-1505ZNE					
125.0	B		131.7	63.0	6.0	4.10	8800	18	R365-1505ZNE					
160.0	C	66.7	166.7	63.0	6.0	5.70	7700	22	R365-1505ZNE					
200.0	C	101.6	206.7	63.0	6.0	10.20	6800	28	R365-1505ZNE					
250.0	C	101.6	256.7	63.0	6.0	11.60	6100	36	R365-1505ZNE					

Inch version

DC CZC _{MS} APMX CNSC Ordering code						Dimensions, inch							CICT MID	
DC	ISO	DBC	DCX	LF	F/lbs	Lbs	RPMX	CICT	MID					
3.000	A		3.264	1.969	4.4	2.53	11600	10	R365-1505ZNE					
4.000	A		4.264	1.969	4.4	3.96	9800	14	R365-1505ZNE					
5.000	B		5.264	2.480	4.4	8.14	8700	18	R365-1505ZNE					
6.000	B		6.264	2.480	4.4	16.94	7900	22	R365-1505ZNE					
8.000	C	4.000	8.264	2.480	4.4	17.01	6800	28	R365-1505ZNE					
10.000	C	4.000	10.264	2.480	4.4	17.07	6000	36	R365-1505ZNE					

