


● Material : Plated steel, Stainless Steel  
● 材質 : SS(三価クロメートメッキ)

## ストレートタイプアダプター

### SR-09 (異径)




接続口金具 : SR-05

SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	Cmm	d <sub>1</sub> φmm	d <sub>2</sub> φmm	Lmm	HEXmm
3×9	G 1/8	R 3/8	15	8	11	4.0	7.0	34	19
6×12	G 1/4	R 1/2	18	8	13	5.5	10.0	39	22
9×19	G 3/8	R 3/4	20	12	15	7.0	16.0	47	27
12×25	G 1/2	R 1	22	12	18	10.0	22.0	52	36

### SR-09 (異径)




接続口金具 : SR-05

SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	Cmm	d <sub>1</sub> φmm	d <sub>2</sub> φmm	Lmm	HEXmm
9×3	G 3/8	R 1/8	10	8	15	7.0	4.0	33	19
12×6	G 1/2	R 1/4	13	10	18	10.0	5.5	41	22
19×9	G 3/4	R 3/8	15	10	20	16.0	7.0	45	27
25×12	G 1	R 1/2	18	12	22	22.0	10.0	52	36

### SR-09GN (アメリカ管用ねじ)




接続口金具 : SR-05

\*印及びSUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm
3	G 1/8	NPT 1/8	10	6	11	4.0	27	14
6	G 1/4	NPT 1/4	13	8	13	5.5	34	19
9	G 3/8	NPT 3/8	15	8	15	7.0	38	22
12	G 1/2	NPT 1/2	18	10	18	10.0	46	27
19	G 3/4	NPT 3/4	20	12	20	16.0	52	36
25	G 1	NPT 1	22	12	22	22.0	56	41
* 32	G 1 1/4	NPT 1 1/4	25	14	24	28.0	63	50
* 38	G 1 1/2	NPT 1 1/2	25	14	24	34.0	63	60
* 50	G 2	NPT 2	30	17	28	45.0	75	70

### SR-09L



接続口金具 : SR-05

SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm
6	G 1/4	R 1/4	50	8	13	5.5	71	19
9	G 3/8	R 3/8	55	8	15	7.0	78	22
12	G 1/2	R 1/2	65	10	18	10.0	93	27
19	G 3/4	R 3/4	80	12	20	16.0	112	36
25	G 1	R 1	85	12	22	22.0	119	41

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。