



T-Max® insert for turning

KNMX



KNUX



				P	M	K
		ISO CODE		4315	5015	H13A
Finishing		16	KNMX 16 04 05 R/L-71	☆	☆	☆
			KNMX 16 04 10 R/L-71	☆	☆	☆
		16	KNUX 16 04 05F R/L12			☆
			KNUX 16 04 05R/L11	☆	☆	☆
			KNUX 16 04 05R/L12	☆	☆	☆
			KNUX 16 04 10F R/L12			☆
			KNUX 16 04 10R/L11	☆	☆	☆
			KNUX 16 04 10R/L12	☆	☆	☆
						☆
						☆

For dimensions, see code key on page I14.

N = Neutral, R = Right hand, L = Left hand

