


ストレートタイプアダプター

- Material : Plated steel, Stainless Steel
- 材質 : SS(三価クロメートメッキ)・SUS304

SR-13 (同径)




接続口金具 : SR-04

*印のSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm	
								SUS	SS
3	G 1/8	R 1/8	10	6	13.0	4.0	29.0	14	
6	G 1/4	R 1/4	13	8	16.0	5.5	37.0	19	
9	G 3/8	R 3/8	15	8	17.5	7.0	40.5	22	
12	G 1/2	R 1/2	18	10	20.0	10.0	48.0	27	
19	G 3/4	R 3/4	20	12	21.5	16.0	53.5	32	36
25	G 1	R 1	22	12	22.5	22.0	56.5	38	41
32	G 1 1/4	R 1 1/4	25	14	27.0	28.0	66.0	46	50
38	G 1 1/2	R 1 1/2	25	14	27.0	34.0	66.0	50	60
50	G 2	R 2	30	17	30.0	45.0	77.0	63	70
65	G 2 1/2	R 2 1/2	33	17	43.0	56.0	93.0	80	
75	G 3	R 3	38	18	43.0	68.0	99.0	90	
* 100	G 4	R 4	45	22	56.0	88.0	123.0	120	

SR-13 (異径)




接続口金具 : SR-04

*印のSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	d ₁ φmm	d ₂ φmm	Lmm	HEXmm
6×9	G 1/4	R 3/8	15	8	16.0	5.5	7.0	39.0	19
9×12	G 3/8	R 1/2	18	10	17.5	7.0	10.0	45.5	22
12×19	G 1/2	R 3/4	20	10	20.0	10.0	16.0	50.0	27
19×25	G 3/4	R 1	22	12	21.5	16.0	22.0	55.5	36
* 25×32	G 1	R 1 1/4	25	14	22.5	22.0	28.0	61.5	46
* 32×38	G 1 1/4	R 1 1/2	25	14	27.0	28.0	28.0	66.0	50
* 38×50	G 1 1/2	R 2	30	14	27.0	33.0	33.0	71.0	60

SR-13 (異径)



接続口金具 : SR-04

*印のSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	d ₁ φmm	d ₂ φmm	Lmm	HEXmm
9×6	G 3/8	R 1/4	13	8	17.5	7.0	5.5	38.5	22
12×9	G 1/2	R 3/8	15	10	20.0	10.0	7.0	45.0	27
19×12	G 3/4	R 1/2	18	12	21.5	16.0	10.0	51.5	32
25×19	G 1	R 3/4	20	12	22.5	22.0	16.0	54.5	38
* 32×25	G 1 1/4	R 1	22	14	27.0	28.0	22.0	63.0	46
* 38×32	G 1 1/2	R 1 1/4	25	14	27.0	28.0	28.0	66.0	50
* 50×38	G 2	R 1 1/2	25	14	30.0	33.0	33.0	69.0	60

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。