


CoroTurn® 107 shank tool for turning

Screw clamp design



Metric version

					Dimensions							MIID
					B	H	LF	WF	HF			
		CZC _{MS}	OHX	Ordering code								
	06	8 x 8	11.0	SCLCR/L 0808D 06	8.0	8.0	60.0	10.0	8.0	0.9	0.04	CCMT 06 02 04
		10 x 10	11.0	SCLCR/L 1010E 06	10.0	10.0	70.0	12.0	10.0	0.9	0.08	CCMT 06 02 04
	09	12 x 12	15.6	SCLCR/L 1212F 09-M	12.0	12.0	80.0	16.0	12.0	3.0	0.56	CCMT 09 T3 08
		16 x 16	16.8	SCLCR/L 1616H 09	16.0	16.0	100.0	20.0	16.0	3.0	0.55	CCMT 09 T3 08
		20 x 20	17.8	SCLCR/L 2020K 09	20.0	20.0	125.0	25.0	20.0	3.0	0.40	CCMT 09 T3 08
	12	20 x 20	21.7	SCLCR/L 2020K 12	20.0	20.0	125.0	25.0	20.0	3.0	0.40	CCMT 12 04 08
		25 x 25	23.7	SCLCR/L 2525M 12	25.0	25.0	150.0	32.0	25.0	3.0	0.80	CCMT 12 04 08
	38	50 x 50	57.4	SCLCR/L5050U38	50.0	50.0	350.0	60.0	50.0	18.7	6.70	CCMT 38 09 32
		60 x 60	57.4	SCLCR/L6060V38	60.0	60.0	400.0	70.0	60.0	18.7	10.90	CCMT 38 09 32
		70 x 70	57.4	SCLCR/L7070V38	70.0	70.0	400.0	80.0	70.0	18.7	14.80	CCMT 38 09 32
		80 x 80	57.4	SCLCR/L8080W38	80.0	80.0	450.0	90.0	80.0	18.7	21.80	CCMT 38 09 32

Inch version

						Ordering code	Dimensions, inch							 	MIID
		CZC _{MS}	OHX	CNSC	B		H	LF	WF	HF					
	1 1/2	2 x 2	2.350	0	SCLCR/L3212K	2.000	2.000	14.000	2.500	2.000	13.8	15.40	CCMT 38 09 32		
		2 1/2 x 2 1/2	2.339	0	SCLCR/L4012X	2.500	2.500	16.000	3.000	2.500	13.8	27.50	CCMT 38 09 32		
		3 x 3	2.354	0	SCLCR/L4812X	3.000	3.000	18.000	3.500	3.000	13.8	44.00	CCMT 38 09 32		
	1/4	3/8 x 3/8	.390	0	SCLCR/L 06 2	.375	.375	2.500	.500	.375	0.7	.18	CCMT 2(1.5)1		
	3/8	1/2 x 1/2	.630	0	SCLCR/L 08 3	.500	.500	3.500	.625	.500	2.2	.35	CCMT 3(2.5)2		
		5/8 x 5/8	.630	0	SCLCR/L 10 3	.625	.625	4.000	.750	.625	2.2	.54	CCMT 3(2.5)2		
		3/4 x 3/4	.634	0	SCLCR/L 12 3B	.750	.750	4.500	1.000	.750	2.2	.88	CCMT 3(2.5)2		
		1 x 1	.740	0	SCLCR/L 16 3D	1.000	1.000	6.000	1.250	1.000	2.2	1.76	CCMT 3(2.5)2		
	1/2	3/4 x 3/4	.894	0	SCLCR/L 12 4B	.750	.750	4.500	1.000	.750	2.2	.88	CCMT 432		
		1 x 1	.894	0	SCLCR/L 16 4D	1.000	1.000	6.000	1.250	1.000	2.2	1.76	CCMT 432		
		1 1/4 x 1 1/4	.894	0	SCLCR/L 20 4D	1.250	1.250	6.000	1.500	1.250	2.2	2.64	CCMT 432		

N = Neutral, R = Right hand, L = Left hand

