



T-Max® P cartridge for turning

Lever clamp design



								Dimensions, mm, inch										MIID		
			CZC _{AS}	DMIN ₁	OHX	CNSC	DSGN	Ordering code	B	H	LF	WF	HF	MHD	MHD2	DAH	LPR			
	12	1/2	12CA	50.0	55.0	0	1	PSKNR/L 12CA-12	16.0	20.0	55.0	20.0	20.0	20.0	7.0	58.1	5.0	0.10	SNMG 12 04 08	
				1.969	2.165		1		.630	.787	2.165	.787	.787	.787	.276	2.287			SNMG 432	
			16CA	55.0	63.0	0	1	PSKNR/L 16CA-12	20.0	25.0	63.0	25.0	25.0	25.0	9.0	66.1	5.0	0.20	SNMG 12 04 08	
				2.165	2.480		1		.787	.984	2.480	.984	.984	.984	.354	2.602			SNMG 432	
							1		.787	1.181	2.756	.984	1.181	1.181	.354	2.909			SNMG 15 06 12	
							1													SNMG 543
	15	5/8	20CA	70.0	70.0	0	1	PSKNR/L 20CA-15	20.0	30.0	70.0	25.0	30.0	30.0	9.0	73.9	5.0	0.20	SNMG 15 06 12	
				2.756	2.756		1		.787	1.181	2.756	.984	1.181	1.181	.354	2.909			SNMG 543	
	19	3/4	25CA	100.0	100.0	0	2	PSKNR 25CA-19	25.0	35.0	100.0	32.0	38.0	30.0	20.0	11.0	104.7	5.0	0.40	SNMG 19 06 12
				3.937	3.937		2		.984	1.378	3.937	1.260	1.496	1.181	.787	.433	4.122			SNMG 643

R = Right hand, L = Left hand

