


## パンチニップル

● Material : Plated steel  
 ● 材質 : SS(三価クロメートメッキ) ● 用途 : 空気、油、蒸気etc. ● 耐圧力 : 低圧~中圧


### 8001



接続アダプター : SR-07・SR-08・SR-17・SR-18


呼び径	ねじT	Amm	Bmm	Cmm	D <sub>1</sub> φmm	D <sub>2</sub> φmm	D <sub>3</sub> φmm	Lmm	HEXmm
6	R ¼	13	8	36	4	6	8.0	57	17
9	R ⅜	15	9	39	6	9	11.0	63	19
12	R ½	18	10	44	9	12	14.0	72	22
19	R ¾	20	12	53	16	19	21.0	85	27
25	R 1	22	12	58	21	25	27.2	92	35
32	R1¼	25	15	65	27	32	35.0	105	46
38	R1½	26	16	76	31	38	41.0	118	50
50	R 2	30	16	79	44	50	52.8	125	63

### 8005



呼び径	ねじT	Amm	Bmm	D <sub>1</sub> φmm	D <sub>2</sub> φmm	D <sub>3</sub> φmm	Lmm	HEXmm
6	G ¼	44	17	4	6	8.0	53	19
9	G ⅜	47	18	6	9	11.0	57	22
12	G ½	53	21	10	12	14.0	65	27
19	G ¾	64	24	16	19	21.0	77	32
25	G 1	71	28	21	25	27.2	86	38
32	G1¼	80	31	28	32	35.0	96	50
38	G1½	91	31	33	38	41.0	107	60
50	G 2	94	33	45	50	52.8	112	70


### 8006



接続アダプター : SR-13・SR-14・SR-17・SR-33・SR-35

呼び径	ねじT	Amm	Bmm	D <sub>1</sub> φmm	D <sub>2</sub> φmm	D <sub>3</sub> φmm	Lmm	HEXmm
6	G ¼	44	17	4	6	8.0	53	19
9	G ⅜	47	18	6	9	11.0	57	22
12	G ½	53	21	10	12	14.0	65	27
19	G ¾	64	24	16	19	21.0	77	32
25	G 1	71	28	21	25	27.2	86	38
32	G1¼	80	31	28	32	35.0	96	50
38	G1½	91	31	33	38	41.0	107	60
50	G 2	94	33	45	50	52.8	112	70

### 8007



接続アダプター : SR-07・SR-09・SR-11・SR-34・SR-36

呼び径	ねじT	Amm	Bmm	D <sub>1</sub> φmm	D <sub>2</sub> φmm	D <sub>3</sub> φmm	Lmm	HEXmm
6	G ¼	47	17	4	6	8.0	53	19
9	G ⅜	51	18	6	9	11.0	57	22
12	G ½	57	21	10	12	14.0	65	27
19	G ¾	69	24	16	19	21.0	77	32
25	G 1	75	28	21	25	27.2	86	38
32	G1¼	85	31	28	32	35.0	96	50
38	G1½	96	31	33	38	41.0	107	60
50	G 2	99	33	45	50	52.8	112	70

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。