


NO.7 Impact Bit



For Impact Driver. This one has a long battery life. Also, the longlasting tool life by heat treatment of Hexagon Shank.

For optimum safety, use a drill at 2,500 rpm or less.



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia

Differences

Combination
Auger Bit



Impact Bit



It can pro-long the battery life with reduced drilling resistance.

Short Type

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia
3	80	45	6.35
4	80	45	6.35
5	90	50	6.35
6 (1/4)	90	50	6.35
7	90	50	6.35
8 (5/16)	90	50	6.35
9	100	60	6.35
10 (3/8)	100	60	6.35
11 (7/16)	100	60	6.35
12	100	60	6.35
13 (1/2)	120	70	6.35
14	120	70	6.35
15	120	70	6.35
16 (5/8)	120	70	6.35
17	120	70	6.35
18 (11/16)	120	70	6.35
19	120	70	6.35
20	130	80	6.35
21 (13/16)	130	80	6.35
22 (7/8)	130	80	6.35
23	130	80	6.35
24 (15/16)	130	80	6.35
25 (1")	130	80	6.35

Middle Type

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia
3	110	60	6.35
4	120	70	6.35
5	140	90	6.35
6 (1/4)	160	100	6.35
7	170	100	6.35
8 (5/16)	170	100	6.35
9	180	110	6.35
10 (3/8)	190	120	6.35
11 (7/16)	190	120	6.35
12	190	120	6.35
13 (1/2)	190	120	6.35
15	200	130	6.35
16 (5/8)	200	130	6.35
18 (11/16)	200	130	6.35
20	205	135	6.35
21 (13/16)	205	135	6.35
22 (7/8)	205	135	6.35
23	205	135	6.35
24 (15/16)	205	135	6.35
25 (1")	205	135	6.35

Long Type

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia
3	185	125	6.35
4	190	130	6.35
5	210	150	6.35
6 (1/4)	210	150	6.35
8 (5/16)	225	165	6.35
9	240	180	6.35
10 (3/8)	250	190	6.35
11 (7/16)	250	190	6.35
12	270	195	6.35
13 (1/2)	270	195	6.35
15	280	205	6.35
16 (5/8)	280	205	6.35
18 (11/16)	310	235	6.35
19	310	235	6.35
20	310	235	6.35
21 (13/16)	310	235	6.35