

A

TOOL HOLDING

Non-machine-specific clamping unit


US TURN

Cylindrical shank with flats to Coromant Capto® clamping unit

B

Segment clamping

Cx-NC2000



C

Metric version

				Dimensions												
CZC _{MS}	CZC _{WS}	CNSC	CXSC	Ordering code	DCON _{MS}	DCON _{WS}	H	LF	WF	HF	HR _Y	CNT				
32	C3	2	2	C3-NC2000-08018-32	32	32	30	18	0	0	26	G1/8	80	35	0.6	
40	C4	2	2	C4-NC2000-10020-40	40	40	37	20	0	0	28	G1/8	80	50	1.0	
50	C4	2	2	C4-NC2000-12020-50	50	40	47	20	0	0	28	G1/8	80	50	1.3	
	C5	2	2	C5-NC2000-12024-50	50	50	47	24	0	0	33	G1/8	80	70	1.6	
60	C5	2	2	C5-NC2000-14024-60	60	50	57	24	0	0	33	G1/8	80	70	2.2	

Inch version

					Dimensions, inch											
CZC _{MS}	CZC _{WS}	CNSC	CXSC	Ordering code	DCON _{MS}	DCON _{WS}	H	LF	WF	HF	HR _Y	CNT	CP BarPSI	Ft/lbs	Lbs	
1 1/4	C3	2	2	C3-NC2000-08018-A20	1.250	1.260	1.181	.709	.000	.000	.930	G1/8	1160	25	1.5	
1 1/2	C4	2	2	C4-NC2000-10020-A24	1.500	1.575	1.457	.787	.000	.000	1.024	G1/8	1160	36	2.2	
2	C4	2	2	C4-NC2000-12020-A32	2.000	1.575	1.850	.787	.000	.000	1.004	G1/8	1160	36	4.1	
	C5	2	2	C5-NC2000-12024-A32	2.000	1.969	1.850	.945	.000	.000	1.220	G1/8	1160	51	4.6	

F

G

H

I



I1



I38