


ネガインサート・マルチコーナタイプ

仕 様	外 観	形 番	在 庫 材 種										数 ナ ー 口	寸 法 (mm)					適 合 ホルダ
			BXM10	BXM20	BXC50	BX310	BX330	BX360	BX380	BX470	BX480	BX930		BX950	内接円 ød	厚さ s	穴径 ød1	コーナ 半径 rε	
汎用		2QP-VNGA160402											2	9.525	4.76	3.81	0.2	3.5	外径用 TACバイト (4-30 ~)
		2QP-VNGA160404	●	●		●	●	●	●	●	●	●	2	9.525	4.76	3.81	0.4	3.1	
2QP-VNGA160408		●	●		●	●	●	●	●	●	●	2	9.525	4.76	3.81	0.8	2.2	内径用 TACバイト (5-37 ~)	
2QP-VNGA160412			●									2	9.525	4.76	3.81	1.2	3		
2QP-VNGA160404-L		●	●			●						2	9.525	4.76	3.81	0.4	3.1		
2QP-VNGA160408-L		●	●			●						2	9.525	4.76	3.81	0.8	2.2		
2QP-VNGA160404-H			●				●	●				2	9.525	4.76	3.81	0.4	3.1		
2QP-VNGA160408-H			●				●	●				2	9.525	4.76	3.81	0.8	2.2		
汎用		4QP-VNGA160404			●							4	9.525	4.76	3.81	0.4	3.1	外径用 TACバイト (4-17 ~)	
		4QP-VNGA160408			●							4	9.525	4.76	3.81	0.8	2.2		
		4QP-VNGA160412										4	9.525	4.76	3.81	1.2	3		
		4QP-VNGA160404-H										4	9.525	4.76	3.81	0.4	3.1		
		4QP-VNGA160408-H										4	9.525	4.76	3.81	0.8	2.2		
		ワイパー 仕様	3QP-WNGA080408	●	●		●	●	●	●		●	●	●	3	12.7	4.76		5.16
汎用		3QP-WNGA080408WL	●	●								3	12.7	4.76	5.16	0.8	2.2	内径用 TACバイト (5-38 ~)	
汎用		6QP-WNGA080408			●							6	12.7	4.76	5.16	0.8	2.2		

※形番名の末尾についたWLの推奨ホルダは 3-6 をご参照下さい。

製品在庫 ●:在庫形番

ネガインサート



標準ホーニング仕様

3-6

材 種	BXM10	BXM20	BXC50	BX310	BX330	BX360	BX380	BX470	BX480	BX910	BX930	BX950
ネガインサート	S01325	S01325	S01325	S01325	S01325	S01325	S01325	T01315	S01325	S01315	S01315	S01325
ポジインサート	S01325	S01325	-	S00515	S00515	S00515	-	T01315	-	S01315	S00515	S00515