

Compact Extra Heavy Duty Castors 1000

RoHS compliant products.

POINT

- Maximum load capacity of both $\phi 80$ and 100 is **1000kg**.
- Thanks to **combination of thrust bearing and ball bearing** in the swivel head, it **moves lightly and turns easily** under a heavy load.
- **Rotates smoothly** after a long-term fixation under a heavy load.

USE EXAMPLE

- For fixed precision machines to be occasionally relocated in a workplace, or moved as production line is rearranged.
 - For heavy duty slow moving carriers.
- ©We'll accept your custom-order. Please feel free to contact us.
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)
©Please feel free to ask about the product weight for each item.



DHJ-LP-100U-MCMO

DHJ Swivel castors



DHJ-80

DHJ-100

- Color/Finish; Zinc plated

DHJB Swivel with stopper



DHJB-80

DHJB-100

DHJ-LP Swivel castors (Long bolt hole type)



DHJ-LP-80

DHJ-LP-100

- Color/Finish; Zinc plated

DHJB-LP Swivel with stopper (Long bolt hole type)



DHJB-LP-80

DHJB-LP-100

DHK Fixed castors




DHK-80

DHK-100

- Color/Finish; Zinc plated

WHEELS JBB ...Radial ball bearing

See P.62 to P.71 for detailed description.



MC (Monomer cast nylon/Blue)
JBB



MCMO (Monomer cast nylon/Black)
JBB