


ストレートタイプアダプター

- Material : Plated steel, Stainless Steel
- 材質 : SS(三価クロメートメッキ)・SUS304

SR-08 (同径)




接続口金具 : SR-01・SR-02

※印のSUS304は32

呼び径	ねじT ₁	ねじT ₂	Amm	dφmm	Lmm	HEXmm
3	G 1/8	Rc 1/8	15	3.0	30	14
6	G 1/4	Rc 1/4	17	5.5	34	19
9	G 3/8	Rc 3/8	19	7.0	38	22
12	G 1/2	Rc 1/2	22	10.0	43	27
19	G 3/4	Rc 3/4	25	16.0	49	※36
25	G 1	Rc 1	27	22.0	53	41
32	G1 1/4	Rc1 1/4	30	28.0	60	50
38	G1 1/2	Rc1 1/2	30	34.0	63	60
50	G 2	Rc 2	36	45.0	71	70

SR-08 (異径)




接続口金具 : SR-01・SR-02

*印及びSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	dφmm	Lmm	HEX ₁ mm	HEX ₂ mm
6×9	G 1/4	Rc 3/8	22	5.5	39	19	22
9×12	G 3/8	Rc 1/2	22	7.0	41	22	27
12×19	G 1/2	Rc 3/4	25	10.0	47	27	36
19×25	G 3/4	Rc 1	27	16.0	51	36	41
* 25×32	G 1	Rc1 1/4	30	22.0	57	41	50
* 32×38	G1 1/4	Rc1 1/2	30	28.0	60	50	60
* 38×50	G1 1/2	Rc 2	36	34.0	68	60	70

SR-08 (異径)



接続口金具 : SR-01・SR-02

*印及びSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	dφmm	Lmm	HEX ₁ mm	HEX ₂ mm
* 6×3	G 1/4	Rc 1/8	14	5.5	31	19	19
9×6	G 3/8	Rc 1/4	17	7.0	36	22	22
12×9	G 1/2	Rc 3/8	19	10.0	41	27	27
19×12	G 3/4	Rc 1/2	22	16.0	46	36	36
25×19	G 1	Rc 3/4	25	22.0	51	41	36
* 32×25	G1 1/4	Rc 1	27	28.0	57	50	41
* 38×32	G1 1/2	Rc1 1/4	30	34.0	63	60	50
* 50×38	G 2	Rc1 1/2	30	45.0	66	70	60