




Stock 38,650 Items

## Rotary Table



HV-8 (chuck sold separately)

HV-8040 (handle)

**Features** •Optimum for arc cutting machining, boring counterbore etc. attached to the table, it can also be used in vertical type.  
•The table rotates 4 degrees per handle rotation.  
**Use** •For accurate angular indexing.  
**Specs** •Surface accuracy less than ±0.02  
**Accessories** •T shape bolt •Handle  
**Origin** •Taiwan

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Table Diameter (mm)	Total Height (mm)	Indexing Precision	Applicable Chuck	Key Groove (mm)	Load Capacity (kg)	SPQ (piece)	Weight (kg)
122-8161	HV-6	¥61,606	¥66,550	152	81	Up to 20 sec	Victor TC130F (5インチ)	11	40	1	12
122-8170	HV-8	¥92,257	¥99,660	200	103	Up to 10 sec	Victor TC165F (6インチ)	14	60	1	29

TRUSCO NAKAYAMA CORPORATION

### Flange/Bolt/Nut Set

**Specs** •Exclusive for front chamfer type scroll chuck

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Compatible Model	Applicable Chuck	SPQ (set)	Weight (kg/set)
239-7986	FLT-0	¥16,089	¥17,380	For HV-6	Victor TC130F (5インチ)	1	2.0
239-7994	FLT-1	¥17,107	¥18,480	For HV-8	Victor TC165F (6インチ)	1	3.5

### Center Calibration Axis for Rotary Table

**Features** •By using the center calibration shaft, centering of the flange and scroll chuck can be performed easily and accurately.  
**Specs** •Acceptable tolerance within ±0.02/100mm

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Axis standard	Compatible flange	SPQ (piece)	Weight (g)
301-1224	MT2-FLT0	¥3,499	¥3,780	MT-2	FLT-0	1	160
301-1232	MT3-FLT1	¥3,823	¥4,130	MT-3	FLT-1	1	230

### T shape bolt

**Features** •T type bolt for adjusting the standard scale position.

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Compatible Model	SPQ (piece)	Weight (g)
762-4794	HV6TB	¥1,851	¥2,000	HV6	1	150
762-4808	HV8TB	¥1,851	¥2,000	HV8	1	150

### Handle

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Compatible Model	SPQ (piece)	Weight (g)
414-9700	HV-6030	¥2,546	¥2,750	For HV-6	1	185.0
414-9718	HV-8030	¥2,546	¥2,750	For HV-8	1	185.0
855-2808	HV-8040	¥ 741	¥ 800	For HV-8	1	25.2

Contact us:0120-509-849 <http://www.orange-book.com/>



FLT-0 (flange/bolt/nut set)



MT2-FLT0 (center calibration axis)



## Manual Indexing Head (divider)



It is a device used for division processing with drilling machines or milling machines.

Turn the table with the lever. The table will stop at the index position where the select pin is set.

### Features

•It is a device to equally divide the peripheral of a workpiece into any number.

It is used for drilling holes equally into the work material (workpieces) (such as disks) with a drilling machine or cutting grooves equally onto a disk with a milling machine. (example)



For the index position, invert the select pin on the table periphery with a screw driver.

