


ホース口金具 (SUS)

● 材質：SUS304


SR-01 管用テーパ雄ねじ



接続アダプター：SR-07・SR-08・SR-17・SR-18

呼び径	ねじT	Amm	Bmm	Dφmm	1W-Lmm	2W-Lmm	HEXmm	外筒内径mm	
								1W	2W
6	R ¼	13	6	4.0	48	53	19	15.0	16.0
9	R ⅜	15	8	6.5	58	64	22	18.0	21.0
12	R ½	18	8	9.5	62	67	27	23.2	24.0
19	R ¾	20	10	15.0	73	83	32	30.0	32.0
25	R 1	22	12	21.5	87	97	41	36.7	39.0
32	R 1¼	25	14	28.0	96	105	50	44.8	48.0
38	R 1½	25	14	33.0	99	111	60	53.8	56.5
50	R 2	30	16	44.0	112	121	70	66.0	68.3

SR-04 管用平行雌ねじ




接続アダプター：SR-13・SR-14・SR-17・SR-33・SR-35

呼び径	ねじT	Amm	Bmm	Dφmm	1W-Lmm	2W-Lmm	HEX 1mm	HEX 2mm	外筒内径mm	
									1W	2W
6	G ¼	17	6	4.0	53	58	19	17	15.0	16.0
9	G ⅜	19	8	6.5	63	69	22	19	18.0	21.0
12	G ½	21	8	9.5	66	71	27	24 ^{**1}	23.2	24.0
19	G ¾	24	10	15.0	78	88	36 ^{**2}	32	30.0	32.0
25	G 1	26	12	21.5	92	102	41	41	36.7	39.0
32	G 1¼	30	14	28.0	102	110	50	50	44.8	48.0
38	G 1½	33	14	33.0	108	120	60	60	53.8	56.5
50	G 2	35	16	44.0	118	127	70	70	66.0	68.3

※¹2Wは22 ※²1Wは32

SR-05 管用平行雌ねじ



接続アダプター：SR-07・SR-09・SR-11・SR-34・SR-36

呼び径	ねじT	Amm	Bmm	Dφmm	1W-Lmm	2W-Lmm	HEX 1mm	HEX 2mm	外筒内径mm	
									1W	2W
6	G ¼	17	6	4.0	53	58	19	17	15.0	16.0
9	G ⅜	19	8	6.5	63	69	22	19 ^{**1}	18.0	21.0
12	G ½	21	8	9.5	66	71	27	24	23.2	24.0
19	G ¾	24	10	15.0	78	88	36 ^{**2}	32	30.0	32.0
25	G 1	26	12	21.5	92	102	41	41	36.7	39.0
32	G 1¼	30	14	28.0	102	110	50	50	44.8	48.0
38	G 1½	33	14	33.0	108	120	60	60	53.8	56.5
50	G 2	35	16	44.0	118	127	70	70	66.0	68.3

※¹2Wは22 ※²1Wは32

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。