

High-speed Steel Hole Saws

The number next to the logo mark indicates items in stock for each brand.

Drills

Coated Carbide Drills

Carbide Drills

High Speed Steel Coated Drills

High Speed Steel Drills

Thin Shaft Drills

Spot Cutters

Taper Shank Drills

Hex Shank Ironsmith Drills

Drill Sets

Drill Cases

Step Drills

Cutters for Magnetic Cutting Unit

Hole Saws

Core Drills

Concrete Drills

Drills

Bits, Cutters for Wood

68700 items in stock
11 cutting tool manufacturers



Stock 38,650 Items

"Hex Shaft TCL Hole Saw"



- Features**
- Cobalt bi-metal blade (SKH 59) and unequal pitch blade realizes stable cutting without chattering, and easy drilling on wood.
 - With spring for discharge.
 - Because of long blade length, it adapts to drilling in a wide range of fields.
 - Guide drilling can be done smoothly with 5mm center drills.
- Materials**
- Blade Part: Cobalt Bi-Metal (SKH59)
 - Center Drills: High Speed Steel (SKH51)
- Origin**
- Japan

Warning

- For cutting more than 2mm, please use the spring removed.
- Blade thickness (cutting width including clipper): 2.07mm *Clipper refers to the saw shape spreading inside/outside.

Iron Plate 3.2mm
Cast Metal 3.2mm
AL Plate 3.2mm
Vinyl Chloride 12mm
Plywood Until throat depth
Gypsum Board Until throat depth
Stainless Plate 1mm

TRUSCO NAKAYAMA CORPORATION										TRUSCO NAKAYAMA CORPORATION									
Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Throat Height (mm)	Shank Diameter (mm)	Blade Thickness (mm)	SPQ (piece)	Weight (g)	Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Throat Height (mm)	Shank Diameter (mm)	Blade Thickness (mm)	SPQ (piece)	Weight (g)
512-7041	TCL-15	¥1,960	¥2,420	15	27	6.35	1.07	5	50	512-7165	TCL-27	¥2,414	¥2,980	27	27	6.35	1.07	5	110
512-7050	TCL-16	¥1,960	¥2,420	16	27	6.35	1.07	5	60	512-7173	TCL-28	¥2,414	¥2,980	28	27	6.35	1.07	5	120
512-7068	TCL-17	¥1,960	¥2,420	17	27	6.35	1.07	5	60	512-7181	TCL-29	¥2,414	¥2,980	29	27	6.35	1.07	5	120
512-7076	TCL-18	¥1,960	¥2,420	18	27	6.35	1.07	5	60	512-7190	TCL-30	¥3,022	¥3,730	30	27	6.35	1.07	5	120
512-7084	TCL-19	¥1,960	¥2,420	19	27	6.35	1.07	5	80	512-7203	TCL-31	¥3,022	¥3,730	31	27	6.35	1.07	5	130
512-7092	TCL-20	¥2,115	¥2,610	20	27	6.35	1.07	5	80	512-7211	TCL-32	¥3,022	¥3,730	32	27	6.35	1.07	5	130
512-7106	TCL-21	¥2,115	¥2,610	21	27	6.35	1.07	5	80	512-7220	TCL-33	¥3,022	¥3,730	33	27	6.35	1.07	5	140
512-7114	TCL-22	¥2,115	¥2,610	22	27	6.35	1.07	5	90	512-7238	TCL-34	¥3,022	¥3,730	34	27	6.35	1.07	5	140
512-7122	TCL-23	¥2,115	¥2,610	23	27	6.35	1.07	5	90	328-7327	TCL-35	¥3,402	¥4,200	35	34	6.35	1.07	5	160
512-7131	TCL-24	¥2,115	¥2,610	24	27	6.35	1.07	5	90	328-7335	TCL-36	¥3,402	¥4,200	36	34	6.35	1.07	3	160
512-7149	TCL-25	¥2,414	¥2,980	25	27	6.35	1.07	5	110	328-7343	TCL-37	¥3,402	¥4,200	37	34	6.35	1.07	3	170
512-7157	TCL-26	¥2,414	¥2,980	26	27	6.35	1.07	5	110	328-7351	TCL-38	¥3,402	¥4,200	38	34	6.35	1.07	3	170




Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Total Length (mm)	Compatible Model	SPQ (piece)	Weight (g)
277-5328	TCL-560	¥495	¥610	5	65	TCL-15 to 38	10	15

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 1,116 Items

Cordless High-speed Steel Hole Saw



- Features**
- Can be used with an impact screwdriver.
 - The blade is only 0.5mm thick, but uses cobalt high-speed steel, which provides acute sharpness and allow quick and easy drilling.
- Materials**
- Blade part: Cobalt high-speed steel
 - Center drill: High-speed steel
- Origin**
- Japan

Iron Plate 2mm
AL Plate 2mm
Vinyl Chloride 5mm
Plywood 12mm
F R P 5mm

UNIKA Co.Ltd										UNIKA Co.Ltd									
Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Throat Height (mm)	Shank Diameter (mm)	Blade Thickness (mm)	SPQ (piece)	Weight (g)	Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Throat Height (mm)	Shank Diameter (mm)	Blade Thickness (mm)	SPQ (piece)	Weight (g)
416-8933	HSSJ-12	¥2,376	¥2,800	12	12	6.35	0.5	5	55	379-4920	HSSJ-27	¥2,885	¥3,400	27	12	6.35	0.5	5	55
416-8941	HSSJ-13	¥2,376	¥2,800	13	12	6.35	0.5	5	57	379-4938	HSSJ-28	¥2,885	¥3,400	28	12	6.35	0.5	5	58
416-8950	HSSJ-15	¥2,376	¥2,800	15	12	6.35	0.5	5	40	379-4946	HSSJ-30	¥3,055	¥3,600	30	12	6.35	0.5	5	61
416-8968	HSSJ-16	¥2,376	¥2,800	16	12	6.35	0.5	5	48	379-4954	HSSJ-32	¥3,225	¥3,800	32	12	6.35	0.5	3	68
416-8976	HSSJ-18	¥2,376	¥2,800	18	12	6.35	0.5	5	52	379-4962	HSSJ-33	¥3,225	¥3,800	33	12	6.35	0.5	3	71
379-4890	HSSJ-21	¥2,461	¥2,900	21	12	6.35	0.5	5	58	379-4971	HSSJ-35	¥3,225	¥3,800	35	12	6.35	0.5	3	75
379-4903	HSSJ-22	¥2,461	¥2,900	22	12	6.35	0.5	5	48	379-4989	HSSJ-38	¥3,734	¥4,400	38	12	6.35	0.5	3	82
379-4911	HSSJ-25	¥2,885	¥3,400	25	12	6.35	0.5	5	52										

Contact us: 03-3864-8711 <http://www.unika.co.jp/>