

Carbide Bars (shank diameter 6mm)

Stock 2,660 Items

5-1133

Prices displayed include 8% tax.



For Air-operated Micro Grinders, see p. 5-474 to 486

TRUSCO Stock 38,650 Items

Carbide Bar

Made to Order RoHS

Com Drawing



Features • Ideal for heavy cutting and grinding as the chip pocket is made large for easier discharge of cutting chips.
Origin • USA

Warning
• The maximum working rotation speed is the recommended value.

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shape	Cutting Diameter x Blade Length x Shaft Diameter x Shaft Length (mm)	Angle (°)	Type	Max Working Rotation Speed (rpm)	Weight (g)
436-5631	TH1C095	¥3,062	¥3,780	Cylinder (coarse cut)	9.5 x 19 x 6 x 45		Brazing	20000	30
436-5658	TH1C127	¥4,973	¥6,140	Cylinder (coarse cut)	12.7 x 25 x 6 x 45		Brazing	15000	54
436-5640	TH1C095E	¥3,467	¥4,280	Cylinder end blade (coarse cut)	9.5 x 19 x 6 x 45		Brazing	20000	30
436-5666	TH1C127E	¥5,427	¥6,700	Cylinder end blade (coarse cut)	12.7 x 25 x 6 x 45		Brazing	15000	54
436-5674	TH2C095	¥3,564	¥4,400	Round point cylinder (coarse cut)	9.5 x 19 x 6 x 45		Brazing	20000	29
436-5682	TH2C127	¥5,654	¥6,980	Round point cylinder (coarse cut)	12.7 x 25 x 6 x 45		Brazing	15000	50
436-5691	TH3C095	¥3,499	¥4,320	Shell (coarse cut)	9.5 x 19 x 6 x 45		Brazing	20000	24
436-5704	TH3C127	¥5,168	¥6,380	Shell (coarse cut)	12.7 x 25 x 6 x 45		Brazing	15000	43
436-5712	TH4C095	¥3,710	¥4,580	Pointed nose (coarse cut)	9.5 x 19 x 6 x 45		Brazing	20000	23
436-5721	TH4C127	¥5,087	¥6,280	Pointed nose (coarse cut)	12.7 x 25 x 6 x 45		Brazing	15000	39
436-5747	TH5C127	¥5,621	¥6,940	Taper (coarse cut)	12.7 x 22 x 6 x 45	28	Brazing	15000	36
436-5755	TH6C095	¥3,499	¥4,320	Egg (coarse cut)	9.5 x 16 x 6 x 45		Brazing	20000	25
436-5763	TH6C127	¥5,184	¥6,400	Egg (coarse cut)	12.7 x 22 x 6 x 45		Brazing	15000	43
436-5771	TH7C095	¥4,277	¥5,280	Round point taper (coarse cut)	9.5 x 27 x 6 x 45	14	Brazing	20000	30
436-5780	TH7C127	¥5,654	¥6,980	Round point taper (coarse cut)	12.7 x 29 x 6 x 45	14	Brazing	15000	49
436-5798	TH8C095	¥2,932	¥3,620	Ball (coarse cut)	9.5 x 8 x 6 x 45		Brazing	20000	18
436-5801	TH8C127	¥3,904	¥4,820	Ball (coarse cut)	12.7 x 11 x 6 x 45		Brazing	15000	27
436-5739	TH51C127	¥7,517	¥9,280	Oval (coarse cut)	12.7 x 32 x 6 x 45		Brazing	15000	48

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Carbide Bar (for aluminum)

Made to Order RoHS

Com Drawing



Features • Sharpness is good, smooth processing can be done.
Origin • USA

Warning
• The maximum working rotation speed is the recommended value.

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shape	Cutting Diameter x Blade Length x Shaft Diameter x Shaft Length (mm)	Angle (°)	Type	Max Working Rotation Speed (rpm)	Weight (g)
384-0832	TA1C060	¥2,430	¥3,000	Cylinder (aluminum cut)	6.0 x 19.0 x 6 x 31.8		100% Carbide	28000	21
384-0841	TA1C095	¥3,208	¥3,960	Cylinder (aluminum cut)	9.5 x 19.0 x 6 x 45.0		Brazing	20000	27
384-0859	TA1C127	¥4,779	¥5,900	Cylinder (aluminum cut)	12.7 x 25.0 x 6 x 45.0		Brazing	15000	50
436-3221	TA1C160	¥6,237	¥7,700	Cylinder (aluminum cut)	16.0 x 25.0 x 6 x 50.0		Brazing	12000	106
436-3230	TA1C190	¥8,521	¥10,520	Cylinder (aluminum cut)	19.0 x 25.0 x 6 x 50.0		Brazing	10000	137
384-0867	TA2C060	¥2,754	¥3,400	Round Point Cylinder (aluminum cut)	6.0 x 19.0 x 6 x 31.8		100% Carbide	28000	21
384-0875	TA2C095	¥3,208	¥3,960	Round Point Cylinder (aluminum cut)	9.5 x 19.0 x 6 x 45.0		Brazing	20000	25
384-0883	TA2C127	¥4,779	¥5,900	Round Point Cylinder (aluminum cut)	12.7 x 25.0 x 6 x 45.0		Brazing	15000	47
436-3248	TA2C190	¥10,603	¥13,090	Round Point Cylinder (aluminum cut)	19.0 x 25.0 x 6 x 50.0		Brazing	10000	124
384-0891	TA3C060	¥2,754	¥3,400	Shell (aluminum cut)	6.0 x 19.0 x 6 x 31.8		100% Carbide	28000	21
384-0905	TA3C095	¥3,402	¥4,200	Shell (aluminum cut)	9.5 x 19.0 x 6 x 45.0		Brazing	20000	23
384-0913	TA3C127	¥4,860	¥6,000	Shell (aluminum cut)	12.7 x 25.0 x 6 x 45.0		Brazing	15000	39
436-3256	TA3C160	¥7,484	¥9,240	Shell (aluminum cut)	16.0 x 25.0 x 6 x 50.0		Brazing	12000	65
436-3264	TA3C190	¥10,384	¥12,820	Shell (aluminum cut)	19.0 x 32.0 x 6 x 50.0		Brazing	10000	93
436-3272	TA6C060	¥3,920	¥4,840	Egg (aluminum cut)	6.0 x 9.5 x 6 x 40.5		100% Carbide	28000	21
436-3281	TA6C095	¥3,888	¥4,800	Egg (aluminum cut)	9.5 x 16.0 x 6 x 45.0		Brazing	20000	23
436-3299	TA6C127	¥4,682	¥5,780	Egg (aluminum cut)	12.7 x 22.0 x 6 x 45.0		Brazing	15000	40
436-3302	TA6C160	¥8,748	¥10,800	Egg (aluminum cut)	16.0 x 25.0 x 6 x 50.0		Brazing	12000	65
436-3311	TA6C190	¥11,340	¥14,000	Egg (aluminum cut)	19.0 x 25.0 x 6 x 50.0		Brazing	10000	89
384-0921	TA7C060	¥3,686	¥4,550	Round Point Taper (aluminum cut)	6.0 x 19.0 x 6 x 31.8		100% Carbide	28000	21
384-0930	TA7C095	¥4,480	¥5,530	Round Point Taper (aluminum cut)	9.5 x 27.0 x 6 x 45.0	14	Brazing	20000	28
384-0948	TA7C127	¥6,124	¥7,560	Round Point Taper (aluminum cut)	12.7 x 29.0 x 6 x 45.0	14	Brazing	15000	43
436-3329	TA7C160	¥10,595	¥13,080	Round Point Taper (aluminum cut)	16.0 x 30.0 x 6 x 50.0	14	Brazing	12000	68
436-3337	TA7C190	¥14,094	¥17,400	Round Point Taper (aluminum cut)	19.0 x 38.0 x 6 x 50.0	14	Brazing	10000	104
384-0956	TA8C060	¥2,722	¥3,360	Ball (aluminum cut)	6.0 x 5.6 x 6 x 45.2		100% Carbide	28000	23
384-0964	TA8C095	¥2,722	¥3,360	Ball (aluminum cut)	9.5 x 8.5 x 6 x 45.0		Brazing	20000	18
384-0972	TA8C127	¥3,791	¥4,680	Ball (aluminum cut)	12.7 x 11.3 x 6 x 45.0		Brazing	15000	27
436-3345	TA8C160	¥7,501	¥9,260	Ball (aluminum cut)	16.0 x 14.0 x 6 x 50.0		Brazing	12000	43
436-3353	TA8C190	¥12,798	¥15,800	Ball (aluminum cut)	19.0 x 18.0 x 6 x 50.0		Brazing	10000	64

Contact us: 0120-509-849 <http://www.orange-book.com/>

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes