


Umbrella Type Brushes with Shaft/Flower Type Brushes

Stock 1,492 Items

5-1385

Prices displayed include 8% tax.



Stock 38,650 Items

Umbrella Type Brush



Features Use

- Easy to mount/replacement with the shaft.
- Umbrella type brush that is easy to operate due to compact and high-speed rotation, excellent usability.
- Since it is an umbrella type, it is optimum for polishing cylindrical inner diameter and bottom part.
- **Working Tool: Variable speed type electric micro grinder.**



123K-2
Hard Steel
Wire



123K-3
Brass



123K-4
Stainless Steel



153K-2
Hard Steel
Wire



153K-3
Brass



153K-4
Stainless Steel

Materials • Shaft: Brass Origin • Japan

Warning

- Air tools cannot be used.
- Please use below The maximum working rotation speed. Please wear protective equipment to use safely.



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Thickness x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	Comments	SPQ (piece)	Weight (g)
415-2531	123K-2	¥1,389	¥1,500	0.12	Hard Steel Wire	12 x 8 x 36 x 3	10000	Delamination and grinding of metal products	1	5.8
415-2549	123K-3	¥1,111	¥1,200	0.15	Brass	12 x 8 x 36 x 3	10000	Polishing of brass, copper products and alloy products	1	6.0
415-2557	123K-4	¥1,241	¥1,340	0.12	Stainless Steel	12 x 8 x 36 x 3	10000	Polishing of stainless steel, aluminum products	1	5.8
415-2565	153K-2	¥1,389	¥1,500	0.12	Hard Steel Wire	15 x 8 x 36 x 3	10000	Delamination and grinding of metal products	1	5.8
415-2573	153K-3	¥1,111	¥1,200	0.15	Brass	15 x 8 x 36 x 3	10000	Polishing of brass, copper products and alloy products	1	6.0
415-2581	153K-4	¥1,241	¥1,340	0.12	Stainless Steel	15 x 8 x 36 x 3	10000	Polishing of stainless steel, aluminum products	1	5.8

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Flower Type Brush



30WF-6

Steel Wire



35WF-6



30SF-6

Stainless Steel



35SF-6

Example

- Warning
- Air tools cannot be used.

- Features • Because the brush is facing the side, it is possible to polish only the crossing hole in a blind hole.
- Use • Ideal for removing burrs on crossing holes. • **Working tool: electric drill, drill press, etc.**
- Materials • Shaft: Steel Origin • Japan

Steel Wire

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Thickness x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
415-2603	20WF-6	¥1,731	¥1,870	0.3	Steel Wire	20 x 10 x 25 x 6	3000	1	40
415-2620	25WF-6	¥1,731	¥1,870	0.3	Steel Wire	25 x 10 x 25 x 6	3000	1	40
415-2646	30WF-6	¥1,944	¥2,100	0.3	Steel Wire	30 x 10 x 35 x 6	3000	1	75
415-2662	35WF-6	¥1,944	¥2,100	0.3	Steel Wire	35 x 10 x 35 x 6	3000	1	80
415-2689	40WF-6	¥2,361	¥2,550	0.3	Steel Wire	40 x 10 x 35 x 6	3000	1	135

Stainless Steel

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Thickness x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
415-2590	20SF-6	¥2,037	¥2,200	0.3	Stainless Steel	20 x 10 x 25 x 6	3000	1	40
415-2611	25SF-6	¥2,037	¥2,200	0.3	Stainless Steel	25 x 10 x 25 x 6	3000	1	40
415-2638	30SF-6	¥2,286	¥2,470	0.3	Stainless Steel	30 x 10 x 35 x 6	3000	1	75
415-2654	35SF-6	¥2,286	¥2,470	0.3	Stainless Steel	35 x 10 x 35 x 6	3000	1	80
415-2671	40SF-6	¥2,991	¥3,230	0.3	Stainless Steel	40 x 10 x 35 x 6	3000	1	135

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Flower Type Brush



83F-2
Hard Steel Wire
(outer diameter 8, 10mm)

103F-3
Brass



123F-4
Stainless Steel
(outer diameter 12, 15mm)

153F-4
Stainless Steel

Example

- Warning
- Air tools cannot be used.

- Features • Flower type brush which is easy to operate due to compact and high speed rotation, excellent in usability.
- Use • Flower type, optimum for polishing cylinder inner diameter and bottom crossing hole.
- **Working Tool: Variable speed type electric micro grinder.** Materials • Shaft: Brass Origin • Japan

Outer Diameter 8, 10mm

SPQ: 1 Piece

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Thickness x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	Comments	Weight (g)
415-2352	83F-2	¥889	¥960	0.1	Hard Steel Wire	8 x 3 x 36 x 3	10000	Delamination and grinding of metal products	3.2
415-2361	83F-3	¥666	¥720	0.1	Brass	8 x 3 x 36 x 3	10000	Polishing of brass, copper products and alloy products	3.2
415-2379	83F-4	¥778	¥840	0.1	Stainless Steel	8 x 3 x 36 x 3	10000	Polishing of stainless steel, aluminum products	3.2
415-2387	103F-2	¥889	¥960	0.1	Hard Steel Wire	10 x 3 x 36 x 3	10000	Delamination and grinding of metal products	3.2
415-2395	103F-3	¥666	¥720	0.1	Brass	10 x 3 x 36 x 3	10000	Polishing of brass, copper products and alloy products	3.2
415-2409	103F-4	¥778	¥840	0.1	Stainless Steel (304)	10 x 3 x 36 x 3	10000	Polishing of stainless steel, aluminum products	3.2

Outer Diameter 12, 15mm

SPQ: 1 Piece

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wire Diameter (mm)	Bristle Material	Outer Diameter x Bristle Thickness x Shaft Length x Shaft Diameter (mm)	Max Working Rotation Speed (rpm)	Comments	Weight (g)
415-2417	123F-2	¥1,389	¥1,500	0.12	Hard Steel Wire	12 x 3 x 31 x 3	10000	Delamination and grinding of metal products	5.8
415-2425	123F-3	¥1,111	¥1,200	0.15	Brass	12 x 3 x 31 x 3	10000	Polishing of brass, copper products and alloy products	6.5
415-2433	123F-4	¥1,241	¥1,340	0.12	Stainless Steel	12 x 3 x 31 x 3	10000	Polishing of stainless steel, aluminum products	5.8
415-2441	153F-2	¥1,389	¥1,500	0.12	Hard Steel Wire	15 x 3 x 31 x 3	10000	Delamination and grinding of metal products	6.0
415-2450	153F-3	¥1,111	¥1,200	0.15	Brass	15 x 3 x 31 x 3	10000	Polishing of brass, copper products and alloy products	6.7
415-2468	153F-4	¥1,241	¥1,340	0.12	Stainless Steel	15 x 3 x 31 x 3	10000	Polishing of stainless steel, aluminum products	6.0

Contact us: 0120-509-849 <http://www.orange-book.com/>