


Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

High Jaw (for both HOWA and KITAGAWA products)



- Features**
- S45C steel which is easy to modify and has suitable hardness is used.
 - Careful processing has been given considering points such as lowering of restoration accuracy (Core run out) after reinstallation and factors causing attachment distortion of the Master Jaw.
- Origin**
- Japan



HN Type (3 Pieces 1 Set)

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Chuck Outer Diameter (inch)	Pitch (mm)	Length (mm)	Width (mm)	Height (mm)	SPQ (set)	Weight (kg/set)
112-9619	HN-6-60-1.5	¥ 9,230	¥ 9,970	6	1.5	75	32	60	1	2.80
112-9627	HN-6-60-3.0	¥ 9,230	¥ 9,970	6	3.0	75	32	60	1	2.80
112-9635	HN-6-90-1.5	¥12,118	¥13,090	6	1.5	75	32	90	1	4.15
112-9643	HN-6-90-3.0	¥12,118	¥13,090	6	3.0	75	32	90	1	4.15
112-9651	HN-8-60-1.5	¥ 9,248	¥ 9,990	8	1.5	90	36	60	1	3.75
112-9660	HN-8-60-3.0	¥ 9,248	¥ 9,990	8	3.0	90	36	60	1	3.75
112-9678	HN-8-90-1.5	¥12,950	¥13,990	8	1.5	90	36	90	1	5.60
112-9686	HN-8-90-3.0	¥12,950	¥13,990	8	3.0	90	36	90	1	5.60
112-9694	HN-8-120-1.5	¥18,458	¥19,940	8	1.5	90	36	120	1	7.80
112-9708	HN-8-120-3.0	¥18,458	¥19,940	8	3.0	90	36	120	1	7.80
112-9716	HN-10-60-1.5	¥12,636	¥13,650	10	1.5	110	40	60	1	5.30
114-0906	HN-10-60-3.0	¥12,636	¥13,650	10	3.0	110	40	60	1	5.30
114-0914	HN-10-90-1.5	¥16,006	¥17,290	10	1.5	110	40	90	1	8.00
114-0922	HN-10-90-3.0	¥16,006	¥17,290	10	3.0	110	40	90	1	8.00
114-0931	HN-10-120-1.5	¥22,180	¥23,960	10	1.5	110	40	120	1	10.70
114-0949	HN-10-120-3.0	¥22,180	¥23,960	10	3.0	110	40	120	1	10.70
114-0957	HN-12-90-1.5	¥21,828	¥23,580	12	1.5	129	50	90	1	11.80
114-0965	HN-12-90-3.0	¥21,828	¥23,580	12	3.0	129	50	90	1	11.80
114-0973	HN-12-120-1.5	¥32,455	¥35,060	12	1.5	129	50	120	1	15.80
114-0981	HN-12-120-3.0	¥32,455	¥35,060	12	3.0	129	50	120	1	15.80


Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**


Soft Jaw (for sale)



- Features**
- S45C steel which is easy to modify and has suitable hardness is used.
 - Careful processing has been given considering points such as lowering of restoration accuracy (Core run out) after reinstallation and factors causing attachment distortion of the Master Jaw.
- Origin**
- Japan



MSE Standard Type (3 pieces 1 set)



HS Powerful Type (3 pieces 1 set)

Standard Type

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Chuck Outer Diameter (inch)	Pitch (mm)	Length (mm)	Width (mm)	Height (mm)	SPQ (set)	Weight (kg/set)
112-7837	MSE-6	¥ 6,850	¥ 7,400	6	-	77	26	35	1	1.30
112-9058	MSE-6-60	¥12,237	¥13,220	6	-	77	26	60	1	2.40
112-7845	MSE-7	¥ 7,794	¥ 8,420	7	-	92	28	38	1	1.85
112-9066	MSE-7-60	¥13,533	¥14,620	7	-	92	28	60	1	3.20
112-9074	MSE-7-90	¥19,968	¥21,570	7	-	92	28	90	1	4.30
112-7853	MSE-9	¥ 9,137	¥ 9,870	9	-	107	34	45	1	3.10
112-9082	MSE-9-60	¥17,376	¥18,770	9	-	107	34	60	1	4.10
112-9091	MSE-9-90	¥22,522	¥24,330	9	-	107	34	90	1	6.10
112-7861	MSE-10	¥12,108	¥13,080	10	-	107	36	50	1	3.60
112-9104	MSE-10-60	¥17,394	¥18,790	10	-	107	36	60	1	4.60
112-9112	MSE-10-90	¥22,522	¥24,330	10	-	107	36	90	1	6.50
112-7870	MSE-12	¥15,210	¥16,430	12	-	125	42	53	1	5.50
112-9121	MSE-12-90	¥25,726	¥27,790	12	-	125	42	90	1	8.90

Powerful Type

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Chuck Outer Diameter (inch)	Pitch (mm)	Length (mm)	Width (mm)	Height (mm)	SPQ (set)	Weight (kg/set)
112-8507	HS-6	¥ 8,322	¥ 8,990	6	-	77	26	35	1	1.3
112-9732	HS-8	¥11,006	¥11,890	8	-	98	32	43	1	2.7
112-8523	HS-9	¥14,867	¥16,060	9	-	114	38	57	1	4.5
112-8531	HS-10	¥18,523	¥20,010	10	-	127	40	58	1	6.1
112-8540	HS-12	¥25,494	¥27,540	12	-	145	42	59	1	8.5

Contact us:0120-509-849 <http://www.orange-book.com/>