

**Single-function
Core Drill** **E&S DC Type**





- Capable of drilling reinforced concrete (cutting up to triple-reinforcement) by dry process without using water.
- Center pin positions only to reduce vibration and noise.
- Uses "10 mm/13 mm chuck combination shank" allowing most drill chucks.
- SDS shanks are also available at the same price.

*Use water for cooling the cutting edge when drilling ceramic tiles and stone.

Effective Length Please refer to the spec table.

Applicable Electric Tool Electric Drill / Percussion Drill (rotating mode)



● Cutting edge shape


Using diamond particles, drilling is performed through grinding the worked on material.



ES-D (Straight-Shank)

	Code	Diameter (mm)	Overall Length (mm)	Effective Length (mm)	
△	ES-D25ST	25	253	150	
△	ES-D29ST	29			
○	ES-D32ST	32			
○	ES-D35ST	35			
○	ES-D38ST	38			
	ES-D40ST	40	252	135	
	ES-D45ST	45			
○	ES-D50ST	50			
	ES-D55ST	55			
	ES-D60ST	60			
○	ES-D65ST	65			
△	ES-D70ST	70			
	ES-D75ST	75			
	ES-D80ST	80			
	ES-D85ST	85			
	ES-D90ST	90			
	ES-D95ST	95	252	135	
	ES-D100ST	100			
	ES-D105ST	105			
	ES-D110ST	110			
	ES-D120ST	120			
	ES-D130ST	130			
	ES-D150ST	150			
	ES-D160ST	160			
	ES-D170ST	170			

Dry Diamond



REINFORCED CONCRETE HARD EXTERIOR PANEL

Resin-based ARTIFICIAL MARBLE MORTAR EXTRUDED CEMENT PANEL
SOFT EXTERIOR PANEL BLOCK / BRICK * CERAMIC TILE

ES-D (SDS-Shank)


	Code	Diameter (mm)	Overall Length (mm)	Effective Length (mm)	
△	ES-D25SDS	25	266	150	
○	ES-D29SDS	29			
○	ES-D32SDS	32			
○	ES-D35SDS	35			
○	ES-D38SDS	38			
△	ES-D40SDS	40	265	135	
	ES-D45SDS	45			
○	ES-D50SDS	50			
	ES-D55SDS	55			
△	ES-D60SDS	60			
○	ES-D65SDS	65			
○	ES-D70SDS	70			
	ES-D75SDS	75			
△	ES-D80SDS	80			
	ES-D85SDS	85			
	ES-D90SDS	90			
	ES-D95SDS	95	265	135	
	ES-D100SDS	100			
	ES-D105SDS	105			
	ES-D110SDS	110			
	ES-D120SDS	120			
	ES-D130SDS	130			
	ES-D150SDS	150			
△	ES-D160SDS	160			
	ES-D170SDS	170			

ES-DH For Hume Pipe (SDS-Shank)

Build to order

	Code	Diameter (mm)	Overall Length (mm)	Effective Length (mm)	
	ES-DH150SDS	150	265	135	
	ES-DH170SDS	170			
	ES-DH200SDS	200			
	ES-DH220SDS	220			

● Handling Method



* ドレス(目立て・目出し)作業についてはP.12をご覧ください。