




- These V-series core drill bits have a cutting edge ideally shaped for hard wall materials, offering both accuracy and efficiency. Basic models are available from narrow diameters to large bores.
- Applying impact with rotation to the cutting edge enables rapid drilling by crushing the material being drilled.

*Use the rotation mode for plasterboards and soft siding boards.

BLOCK		BRICK	
MORTAR	PLASTERBOARD	HARD EXTERIOR PANEL	SOFT EXTERIOR PANEL

Applicable Electric Tool **Percussion Drill**

25 - 55mm



60 - 170mm



UR-V (Set)

Code	Code		Diameter (mm)	Effective Length (mm)	Center Drill (code)
	ST-Shank	SDS-Shank			
UR21-V025ST	UR21-V025SD	25	170	URCD-T250	
UR21-V029ST	UR21-V029SD	29			
UR21-V032ST	UR21-V032SD	32			
UR21-V035ST	UR21-V035SD	35			
UR21-V038ST	UR21-V038SD	38			
UR21-V040ST	UR21-V040SD	40			
UR21-V045ST	UR21-V045SD	45			
UR21-V050ST	UR21-V050SD	50			
UR21-V055ST	UR21-V055SD	55			
UR-V60ST	UR-V60SD	60	130	2CB-210	
UR-V65ST	UR-V65SD	65			
UR-V70ST	UR-V70SD	70			
UR-V75ST	UR-V75SD	75			
UR-V80ST	UR-V80SD	80			
UR-V85ST	UR-V85SD	85			
UR-V90ST	UR-V90SD	90			
UR-V95ST	UR-V95SD	95			
UR-V100ST	UR-V100SD	100			
UR-V105ST	UR-V105SD	105			
UR-V110ST	UR-V110SD	110			
UR-V115ST	UR-V115SD	115			
UR-V120ST	UR-V120SD	120			
UR-V130ST	UR-V130SD	130			
UR-V150ST	UR-V150SD	150			
UR-V155ST	UR-V155SD	155			
UR-V160ST	UR-V160SD	160			
UR-V170ST	UR-V170SD	170			

UR-V (Body)

Code	Diameter (mm)
UR21-V025B	25
UR21-V029B	29
UR21-V032B	32
UR21-V035B	35
UR21-V038B	38
UR21-V040B	40
UR21-V045B	45
UR21-V050B	50
UR21-V055B	55
UR-V60B	60
UR-V65B	65
UR-V70B	70
UR-V75B	75
UR-V80B	80
UR-V85B	85
UR-V90B	90
UR-V95B	95
UR-V100B	100
UR-V105B	105
UR-V110B	110
UR-V115B	115
UR-V120B	120
UR-V130B	130
UR-V150B	150
UR-V155B	155
UR-V160B	160
UR-V170B	170

UR-V (Center Drill)

Code	Diameter (mm)	Overall Length (mm)	Core Drill Size (mm)
URCD-T250	10.0	250	25~55
2CB-210		210	60~170

UR21 (Shank Assembly)

For codes, specifications, and availability look at the **UR21** shank assembly availability list (P. 20).

Diameter 25 ~ 55 mm

All replacement blades and all sizes (diameter: 25 - 55 mm) are available for one type shank assembly.

Percussion Body
UR21-V025B ~ V055B

Center Drill
URCD-T250



SDS-Shank
UR25/55FSD

ST-Shank
UR25/55FST

Diameter 60 ~ 170 mm

For a diameter of 60 mm or more, a shank assembly of a corresponding size is required for each size.

Percussion Body
UR-V60B ~ V170B

Center Drill
2CB-210



SDS-Shank
2CB60FSD ~ 170FSD

ST-Shank
2CB60FST ~ 170FST