

Flap Wheels with Shaft (shaft diameter 3mm, 6mm)

Stock 1,275 Items

5-1037

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

Bevel Gear Flap Wheel (shaft diameter 6mm)



RoHS

Com Drawing SDS



CP Type

- Features**
- For general metal. Since the polishing cloth is implanted in a shape that covers the base, it is possible to simultaneously polish the two sides of the bottom and the side. A product that improves the efficiency of grinding operation and versatility.
 - No clogging, uniform polishing is possible up to the end.
 - Always be polished with a new abrasive grain surface by autogenous action.
 - The burning and strain of the object to be polished does not come out by the air cooling action.
- Use**
- For polishing of bottom, corner, flat surface, curve surface.
 - Working Tool: Straight-type grinder.
- Origin**
- Japan



Estimated Unit Price per Piece
¥810 to ¥1,350

Outer Diameter 40mm

Specs •Max Working Rotation Speed: 5000rpm

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	Weight (g/box)
117-8113	CP43	40	¥4,050	¥5,000	40	40 x 30 x 6 x 40	Approx. 37	5	260
117-8121	CP43	60	¥4,050	¥5,000	60	40 x 30 x 6 x 40	Approx. 55	5	263
117-8156	CP43	80	¥4,050	¥5,000	80	40 x 30 x 6 x 40	Approx. 63	5	264
117-8164	CP43	100	¥4,050	¥5,000	100	40 x 30 x 6 x 40	Approx. 69	5	255
117-8172	CP43	120	¥4,050	¥5,000	120	40 x 30 x 6 x 40	Approx. 70	5	265

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	Weight (g/box)
117-8199	CP43	150	¥4,050	¥5,000	150	40 x 30 x 6 x 40	Approx. 74	5	267
117-8202	CP43	180	¥4,050	¥5,000	180	40 x 30 x 6 x 40	Approx. 78	5	266
117-8211	CP43	240	¥4,050	¥5,000	240	40 x 30 x 6 x 40	Approx. 87	5	255
117-8229	CP43	320	¥4,050	¥5,000	320	40 x 30 x 6 x 40	Approx. 99	5	252
118-1297	CP43	400	¥4,050	¥5,000	400	40 x 30 x 6 x 40	Approx. 98	5	251

Outer Diameter 60mm

Specs •Max Working Rotation Speed: 3000rpm

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	Weight (g/box)
118-1301	CP64	40	¥6,748	¥8,330	40	60 x 40 x 6 x 40	Approx. 59	5	568
118-1319	CP64	60	¥6,748	¥8,330	60	60 x 40 x 6 x 40	Approx. 88	5	538
118-1327	CP64	80	¥6,748	¥8,330	80	60 x 40 x 6 x 40	Approx. 104	5	523
118-1335	CP64	100	¥6,748	¥8,330	100	60 x 40 x 6 x 40	Approx. 112	5	543
118-1343	CP64	120	¥6,748	¥8,330	120	60 x 40 x 6 x 40	Approx. 112	5	563

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	Weight (g/box)
118-1351	CP64	150	¥6,748	¥8,330	150	60 x 40 x 6 x 40	Approx. 117	5	568
118-1360	CP64	180	¥6,748	¥8,330	180	60 x 40 x 6 x 40	Approx. 123	5	568
118-1378	CP64	240	¥6,748	¥8,330	240	60 x 40 x 6 x 40	Approx. 147	5	533
118-1386	CP64	320	¥6,748	¥8,330	320	60 x 40 x 6 x 40	Approx. 157	5	528
118-1394	CP64	400	¥6,748	¥8,330	400	60 x 40 x 6 x 40	Approx. 158	5	528

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

"GP Top" Mini" (M7 x P0.75 screw hole-equipped type)

RoHS

Com Drawing SDS



GP3007

- Features**
- Rich in particle size variation, it is a versatile type that covers from rough finishing to finish polishing.
 - Prevents polishing burns which are a disadvantage of elastic whetstones and has high grinding performance as well as a 5- to 6-fold long life.
 - There is cushioning property compared with grinding stone, hitting softly to workpiece.
- Use**
- Optimum for removal of spot welding burr of automobiles, home electric appliance product etc., especially for polishing of molding die.
 - For general metal. •Working tool: air-operated grinder.
- Specs**
- Maximum working peripheral velocity: 47.1m/s (2826m/min)
- Accessories**
- 3mm shaft adapter (1 piece per box)
- Origin**
- Japan



Item No.	Applicable working tool (example)
GP3007	UHT: MAG-093N (MAG-123N) VESSEL: GT-MG25-12CR (GT-MG25-9CR) MURAKI: M-109 (M-111)

*By mounting this 3mm shaft adapter, a shaft can be attached to collet chuck type disc grinders.

Estimated Unit Price per Piece
¥389


Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer diameter x width x screw diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
118-1602	GP3007	40	¥1,944	¥2,400	40	30 x 8 x M7 (P0.75)	30000	28	5	20	50
118-1611	GP3007	60	¥1,944	¥2,400	60	30 x 8 x M7 (P0.75)	30000	28	5	20	45
118-1629	GP3007	80	¥1,944	¥2,400	80	30 x 8 x M7 (P0.75)	30000	28	5	20	40
118-1637	GP3007	100	¥1,944	¥2,400	100	30 x 8 x M7 (P0.75)	30000	28	5	20	40
118-1645	GP3007	120	¥1,944	¥2,400	120	30 x 8 x M7 (P0.75)	30000	28	5	20	40
118-1653	GP3007	150	¥1,944	¥2,400	150	30 x 8 x M7 (P0.75)	30000	28	5	20	40
118-1661	GP3007	180	¥1,944	¥2,400	180	30 x 8 x M7 (P0.75)	30000	28	5	20	40
118-1670	GP3007	240	¥1,944	¥2,400	240	30 x 8 x M7 (P0.75)	30000	28	5	20	40
118-1688	GP3007	320	¥1,944	¥2,400	320	30 x 8 x M7 (P0.75)	30000	28	5	20	40
118-1696	GP3007	400	¥1,944	¥2,400	400	30 x 8 x M7 (P0.75)	30000	28	5	20	40

3mm Shaft Adapter

Features •By mounting this, a shaft can be attached to collet chuck type disc grinders.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	SPQ (piece)	Weight (g)
798-4383	GPTMJ3-1P	¥405	¥500	1	2.7

Contact us:0120-509-849 <http://www.orange-book.com/>



GPTMJ3-1P (3mm shaft adapter)

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes