

Air Impact Wrenches Double Hammer Powerful tightening with air motor **VESSEL**


Machine Bolt Dia. **6~8mm** Corner type impact wrench.



No. GT-S60CW

9.5 Pin-lock

④ Adjust dial



Machine Bolt Dia. **6~8mm** For powerful constant fastening. Excellent durability.



No. GT-S65W

9.5 Pin-lock

④ Adjust dial



No. GT-P65W

9.5 Pin-lock

③ Adjust dial



No. GT-S70WK

9.5 Pin-lock

④ Adjust dial

Noise reducer/Rear exhaust

Machine Bolt Dia. **8~10mm** For powerful constant fastening.



No. GT-P80W

12.7 Pin-lock

③ Adjust dial

Machine Bolt Dia. **12~16mm** For powerful constant fastening.



No. GT-P14W

12.7 Pin-lock

④ Adjust dial

Model No.	Capacity Ordinary Bolt Dia. (mm)	Torque Range (N·m)	Max. Torque (N·m)	No Load Speed (rpm)	Air Consumption (ml/min)	Hose Coupling	Air Hose Inner Dia. (mm)	Overall length (mm)	Weight (kg)	Accessories			EDP No.
										Socket	Plug	L-wrench	
GT-P65W	6~8	49~121.6	140.5	8,500	0.38	Rc 1/4	6.35	146	1.43	A/F10	BPB-2	H4	324038
GT-S65W	6~8	49~121.6	140.5	7,500	0.35	Rc 1/4	6.35	210	1.3	A/F10	BPB-2	H4	324008
GT-S70WK	6~8	85~176.5	193.5	7,000	0.39	Rc 1/4	6.35	231	1.3	—	BPB-2	H4	324017
GT-S60CW	6~8	25~47	51.5	7,300	0.35	Rc 1/4	6.35	255	1.87	A/F10	BPB-2	H4	324011
GT-P80W	8~10	49~259.8	295.3	7,500	0.4	Rc 1/4	6.35	164	1.89	A/F14	BPB-2	H4	324048
GT-P14W	12~16	49~421.6	505.0	6,400	0.47	Rc 1/4	9.5	200	3.2	A/F22	BPB-2	H5	324073

*Air pressure: 0.6MPa *Overall length and Weight: Accessories not included. *Capacity is listed as instant reference and depends on operation conditions.