

Cylindrical Nuts

Type	Material	Surface Treatment
RBNT	SUS304	-

RoHS 10

Part Number	D	L	W	Unit Price
RBNT	3	6	8	1
	4	8	10	
	5	10	11	
	6	12	12	1.5
	8	14	16	
	10	18	20	
12	20	24	2.5	

Part Number
RBNT10

Flanged Nuts

Type	Material	Surface Treatment
FRNUT	SWCH10R	Trivalent Chromate
FRSNUT	SUS304 Equivalent	-

RoHS 10

⊕ Not serrated

Part Number	Type	M	Coarse	D	B	(e)	T	T1 (Min.)	FRNUT		FRSNUT	
									Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
FRNUT FRSNUT	3	0.5	8	5.5	6.3	3.7	1					
	4	0.7	10	7	8	4.5	1.1					
	5	0.8	12	8	9.2	5.5	1.1					
	6	1	13	10	11.5	6	1.5					
	8	1.25	17	12	13.8	7.5	1.5					
	10	1.5	19	14	16.2	9	1.8					

Ordering Example
Part Number
FRNUTS


Knurled Thumb Nuts with Side Holes

Type		Material	Surface Treatment
Coarse	CRNT	S45C	Black Oxide
Fine	CRNTS	SUS304	-

RoHS 10

Features

- The nuts can be tightened with hex key wrenches using the holes, made to fit the wrenches, on the side.
- The tapped holes can be used for retaining set screws.
- Use in spaces where standard hex wrenches cannot reach.



Part Number	Type	M	MxPitch Coarse	MxPitch Fine	D	T	d	Applicable Hex Key Wrench Size	M1	C	Unit Price			
											CRNT	CRNTS	SCRNT	SCRNTS
CRNT CRNTS SCRNT SCRNTS	10	10x1.5	10x1.0	25	8	4.6	5	4	4	0.5				
	12	12x1.75	12x1.0	30	10	5.8	6	5	5					
	16	16x2	16x1.5	38	12	6.9	7	6						
	20	20x2.5	-	45	16	9.2	8	8	6	1				
	24	24x3	-	50	18	9	8		8					
	30	30x3.5	-	60	20	11.5	10	10						

Part Number
CRNT10

T-Nuts

Type	Material	Surface Treatment
Standard Type	NTS	SS400
Configurable	NTSF	Trivalent Bright Chrome Plating / Black Oxide

RoHS 10

Standard Type

Part Number	Type	M (Coarse)	A	B	C	E	F	d1	Unit Price	Volume Discount Rate
NTS	3	3.9	7	5	3	2.0	3.5		1 - 49 pc(s)	50 - 500 pcs.
	4	4.8	8	6.5	4	2.5	4.5			
	5	5.8	10	8	5	3	5.5			
	6	7.7	13	9.5	6	3.5	7			
	8	9.7	13	10.5	6	4.5	9			
	10	11.7	16	12.5	7	5.5	11			
	12	17.6	25	18.5	10	8.5	14			
	16	21.6	32	24.5	14	10.5	18			
20	24.6	35	30.5	20	10.5	22				

Configurable

Part Number	Type	M (Coarse)	A	E	F	B	d1	Unit Price	Volume Discount Rate
NTSF	3	3.9-17.6	3-10	2-8.5	7	3.5		1 - 9 pc(s)	10 - 50 pcs.
	4				8	4.5			
	5				10	5.5			
	6				13	7			
	8				13	9			
	10				16	11			
12	25	14							

Ordering Example
Part Number - NTS8 - A9.5 - E5.2 - F4.8
NTSF12 - A9.5 - E5.2 - F4.8