


# Mini Rods


## Selectable Tips




End Shape			Material	Hardness
Sphere	Tapered	Taper SR		
MRS HQ	MRS HT	MRS HR	SKH51	58HRC~
MRS SQ	MRS ST	MRS SR	SUS440C	56HRC~
MRS GQ	MRS GT	-	SUS304	-

$6.3 / \left( \frac{0.4}{G} \right)$


**Sphere**



**Tapered**



**Taper SR**



RoHS10

### Sphere Type

Part Number	0.1mm Increment		Unit Price		
	D	L	SKH51 MRS HQ	SUS440C MRS SQ	SUS304 MRS GQ
MRS HQ MRS SQ MRS GQ	2.0~2.9	5.0~20.0			
		20.1~50.0			
		50.1~100.0			
	3.0~3.9	5.0~20.0			
		20.1~50.0			
		50.1~100.0			
4.0~5.0	8.0~20.0				
	20.1~50.0				
	50.1~100.0				

### Tapered Type

Part Number	0.1mm Increment		RL D-2 (RLtan15°)≥0.2	Unit Price			
	D	L		SKH51 MRS HT	SUS440C MRS ST	SUS304 MRS GT	
MRS HT MRS ST MRS GT	2.0~2.9	5.0~20.0	0.5~10				
		20.1~50.0					
		50.1~100.0					
	3.0~3.9	5.0~20.0					
		20.1~50.0					
		50.1~100.0					
	4.0~5.0	5.0~20.0					
		20.1~50.0					
		50.1~100.0					

### Taper SR Type

Part Number	0.1mm Increment		SR	a (Reference)	Unit Price			
	D	L			SKH51 MRS HR	SUS440C MRS SR		
MRS HR MRS SR	2.0~2.9	8.0~20.0	0.5	2.4~4.1				
		20.1~50.0						
		50.1~100.0						
	3.0~3.9	8.0~20.0		4.2~6.0				
		20.1~50.0						
		50.1~100.0						
	4.0~5.0	8.0~20.0		1	4.7~6.6			
		20.1~50.0						
		50.1~100.0						



Ordering Example  
 Part Number - D - L - RL  
 MRS HT - D3.5 - L100.0 - RL5

ⓘ a dimensions vary within values listed above according to D dimensions.