



Thick-Walled Ground Stainless Steel Hollow Tubes

Straight



PSTS



$\sqrt[6]{\frac{63}{\sqrt{1.6}}}$




L Dimension Tolerance or More or Less		
or More	or Less	Tolerance
10	30	±0.2
31	120	±0.3
121	400	±0.5
401	1000	±0.8
1001	1200	±1.2

Material: SUS304

Part Number			L 1mm increment	t	(d ^{+0.5})	Unit Price				
Type	D	h8				L10~200	L201~400	L401~600	L601~800	L801~1000
PSTS	6	0 -0.018	10~600	1.5	3					
	8A			1.5	5					
	8	0		2	4					
	10A	-0.022		1.5	7					
	10		10~800	2	6					
	12A			2	8					
	12			3	6					
	12B			4	4					
	15B	0	10~1000	1.5	12					
	15A	-0.027		2	11					
	15			3	9					
	16			3	10					
	20A			2.5	15					
	20			4	12					
	20B			6	8					
	25A	0		3	19					
	25	-0.033	5	15						
	30A		3	24						
	30		5	20						
	35		5	25						
40	0	10~1200	5	30						
45	-0.039		5	35						
50			5	35						
			8	34						

 **Ordering Example** Part Number - L
PSTS15 - 173

 **Alterations** Part Number - L - (MF, WF, VC, LKC)
PSTS15 - 173 - WF17

Alterations Code	Side Tapped		V Groove	L Dimension Tolerance																																					
	MF	WF	VC	LKC																																					
Spec.	 <p>MF, WF = 1mm Increment Ordering Code MF12 ⊗ Not applicable to D6, 8A, 10A and 15B</p> <table border="1"> <thead> <tr> <th>D</th> <th>Side Tap Dia.</th> </tr> </thead> <tbody> <tr> <td>8, 10, 12, 12A, 12B, 15, 15A, 16</td> <td>M3</td> </tr> <tr> <td>20, 20A, 20B, 25, 25A, 30, 30A</td> <td>M4</td> </tr> <tr> <td>35, 40, 45, 50</td> <td>M5</td> </tr> </tbody> </table>		D	Side Tap Dia.	8, 10, 12, 12A, 12B, 15, 15A, 16	M3	20, 20A, 20B, 25, 25A, 30, 30A	M4	35, 40, 45, 50	M5	 <p>VC = 1mm Increment Ordering Code VC15 ⊗ Not applicable to D6, 8A, 10A and 15B</p> <table border="1"> <thead> <tr> <th>D</th> <th>h</th> <th>d</th> </tr> </thead> <tbody> <tr> <td>8</td> <td rowspan="3">4</td> <td rowspan="3">0.75</td> </tr> <tr> <td>10</td> </tr> <tr> <td>12, 12A</td> </tr> <tr> <td>15, 15A, 16, 20, 20A, 20B</td> <td>5</td> <td>1.0</td> </tr> <tr> <td>25, 25A, 30, 30A</td> <td>6</td> <td rowspan="2">1.5</td> </tr> <tr> <td>35, 40</td> <td>8</td> </tr> <tr> <td>45, 50</td> <td>12</td> <td>2.0</td> </tr> </tbody> </table>	D	h	d	8	4	0.75	10	12, 12A	15, 15A, 16, 20, 20A, 20B	5	1.0	25, 25A, 30, 30A	6	1.5	35, 40	8	45, 50	12	2.0	 <p>L Dimension Tolerance Ordering Code LKC</p> <table border="1"> <thead> <tr> <th>L</th> <th>L Tolerance</th> </tr> </thead> <tbody> <tr> <td>10~ 200</td> <td>+0.05 0</td> </tr> <tr> <td>201~ 500</td> <td>+0.2 0</td> </tr> <tr> <td>501~ 800</td> <td>+0.5 0</td> </tr> <tr> <td>801~1200</td> <td>+0.8 0</td> </tr> </tbody> </table>	L	L Tolerance	10~ 200	+0.05 0	201~ 500	+0.2 0	501~ 800	+0.5 0	801~1200	+0.8 0
	D	Side Tap Dia.																																							
8, 10, 12, 12A, 12B, 15, 15A, 16	M3																																								
20, 20A, 20B, 25, 25A, 30, 30A	M4																																								
35, 40, 45, 50	M5																																								
D	h	d																																							
8	4	0.75																																							
10																																									
12, 12A																																									
15, 15A, 16, 20, 20A, 20B	5	1.0																																							
25, 25A, 30, 30A	6	1.5																																							
35, 40	8																																								
45, 50	12	2.0																																							
L	L Tolerance																																								
10~ 200	+0.05 0																																								
201~ 500	+0.2 0																																								
501~ 800	+0.5 0																																								
801~1200	+0.8 0																																								