



パイプニップル SUS304

両ねじ




片ねじ




呼び	a	f (最小寸法)	φA	バレルニップル (L)	ロングニップル L							
					50	65	75	100	125	150	200	
6	1/8	3.97	2.5	10.5	24.5	50	65	75	100	125	150	200
8	1/4	6.01	3.7	13.8	27.5	50	65	75	100	125	150	200
10	3/8	6.35	3.7	17.3	28.5	50	65	75	100	125	150	200
15	1/2	8.16	5	21.7	34.5	50	65	75	100	125	150	200
20	3/4	9.53	5	27.2	38.5	50	65	75	100	125	150	200
25	1	10.39	6.4	34	42.5	50	65	75	100	125	150	200
32	1 1/4	12.70	6.4	42.7	50.5	-	-	75	100	125	150	200
40	1 1/2	12.70	6.4	48.6	50.5	-	-	75	100	125	150	200
50	2	15.88	7.5	60.5	58.5	-	-	75	100	125	150	200
65	2 1/2	17.46	9.2	76.3	70.5	-	-	-	100	125	150	200
80	3	20.64	9.2	89.1	78.5	-	-	-	100	125	150	200
100	4	25.40	10.4	114.3	90.5	-	-	-	100	125	150	200

パイプソケット類 SUS304




ストレートねじ (S)

呼び	L	φA
6	1/8	20
8	1/4	25
10	3/8	26
15	1/2	33
20	3/4	36
25	1	43
32	1 1/4	48
40	1 1/2	48
50	2	56
65	2 1/2	65
80	3	70
100	4	84




ストレートねじ厚肉 (SJ)

呼び	L	φA
8	1/4	27
10	3/8	28
15	1/2	37
20	3/4	39
25	1	46
32	1 1/4	51
40	1 1/2	51
50	2	60




ホースニップル (丸) (CHNI)

呼び	L	φA	E×数
6	1/8	41	10.5
8	1/4	41	13.8
10	3/8	42	17.3
15	1/2	52	21.7
20	3/4	55	27.2
25	1	60	34
32	1 1/4	66	42.7
40	1 1/2	70	48.6
50	2	80	60.5




テーパねじ (SPT)

呼び	L	φA
6	1/8	23
8	1/4	29
10	3/8	30
15	1/2	38
20	3/4	40
25	1	45
32	1 1/4	51
40	1 1/2	54
50	2	64



ハーフソケット ストレート (HSS)

呼び	L	φA
6	1/8	12
8	1/4	15
10	3/8	16
15	1/2	20
20	3/4	21
25	1	25
32	1 1/4	28
40	1 1/2	28
50	2	34
65	2 1/2	39
80	3	42
100	4	50



ハーフテーパソケット (HPTS)

呼び	L	φA
8	1/4	18
10	3/8	18
15	1/2	21
20	3/4	21
25	1	25
32	1 1/4	27
40	1 1/2	27
50	2	32

単位 : mm