












Photomicrosensors

Mini Type


⊗ Not available outside of Japan.

Rails for Mounting  **P.2077~2083** Slit Cams for Indexing  **P.2075**

FPMK24 (Standard)	FPMF24 (Type F)	FPMU24 (Type U)	FPML24 (Type L)	FPMR24 (Type R)																				
																								
<p>FPMK24 (Standard)</p>  <p>Optical Axis</p> <p>Operation Indicator (Red)</p> <p>Ø2.7 Cable 1m</p>	<p>FPMF24 (Type F)</p>  <p>Optical Axis</p> <p>Operation Indicator (Red)</p> <p>Ø2.5 Mounting Hole</p> <p>Ø2.7 Cable 1m</p>	<p>FPMU24 (Type U)</p>  <p>Optical Axis</p> <p>Operation Indicator (Red)</p> <p>Ø2.7 Cable 1m</p> <p>2 - Ø2.5 Mounting Hole</p>	<p>FPML24 (Type L)</p>  <p>Optical Axis</p> <p>Operation Indicator (Red)</p> <p>Ø2.7 Cable 1m</p> <p>2 - Ø2.5 Mounting Hole</p>	<p>FPMR24 (Type R)</p>  <p>Optical Axis</p> <p>Operation Indicator (Red)</p> <p>Ø2.5 Mounting Hole</p>																				
<table border="1"> <thead> <tr> <th>Shape</th> <th>Part Number</th> <th>Detection Distance</th> <th>Output</th> <th>Operation Mode</th> <th>Unit Price</th> </tr> </thead> <tbody> <tr> <td>Standard</td> <td>FPMK24</td> <td rowspan="5">5mm (Fixed)</td> <td rowspan="5">NPN Transistor Open Collector</td> <td rowspan="5">Light Seen - ON Light Blocked - ON Equipped 2 Outputs</td> <td rowspan="5"></td> </tr> <tr> <td>Type L</td> <td>FPML24</td> </tr> <tr> <td>Type F</td> <td>FPMF24</td> </tr> <tr> <td>Type R</td> <td>FPMR24</td> </tr> <tr> <td>Type U</td> <td>FPMU24</td> </tr> </tbody> </table> <p> Ordering Example Part Number FPML24</p>					Shape	Part Number	Detection Distance	Output	Operation Mode	Unit Price	Standard	FPMK24	5mm (Fixed)	NPN Transistor Open Collector	Light Seen - ON Light Blocked - ON Equipped 2 Outputs		Type L	FPML24	Type F	FPMF24	Type R	FPMR24	Type U	FPMU24
Shape	Part Number	Detection Distance	Output	Operation Mode	Unit Price																			
Standard	FPMK24	5mm (Fixed)	NPN Transistor Open Collector	Light Seen - ON Light Blocked - ON Equipped 2 Outputs																				
Type L	FPML24																							
Type F	FPMF24																							
Type R	FPMR24																							
Type U	FPMU24																							


 **Example**

The slit on a rotating disc detects the home position.



Screws for Photo Sensors (M2)

FKN



M2xP0.4

4.0

3.5

1.3

(1.8)


Screw Material: Carbon Steel for Mechanical Structure
Screw: JIS B1188

Washer Spring Washer: JIS B1251

Surface Treatment Chromate (Yellow)

RoHS 10

Part Number	Unit Price	Volume Discount Rate
Type	M-L	1 - 5 pcs(5), 6 - 1000
FKN	2-6	
	2-8	
	2-10	
	2-12	

 **Ordering Example** Part Number **FKN2-8**

⊗ For orders larger than indicated quantity, please check with WOS.