



Tabletop Leveling Mounts



NFB



MMaterial: PP Resin (Pad)
SS400 (Thread)

SSurface Treatment: Trivalent Chromate

RoHS 10


Ⓢ Screws and pads are integrated. Ⓜ Hex nut included.

Part Number	M Coarse Thread	A				ℓ	E	Allowable Load (kN)	Unit Price
Type	D								
NFB	20	5	14	18	23	28	4	7	0.7
		6	17	22	27	32	5	8	1.0
	30	6	17	22	27	32	5	8	1.2
		8	21	26	31	36	6.5	9.5	1.8
40	8	21	26	31	36	6.5	9.5	2.0	
	10	25	30	35	40	8	9.5	2.1	

Ordering Example: Part Number - M - A
NFB30 - 6 - 27


Features: New product with a leveling function. Less slippery than the existing products.

Grip Type



RoHS 10

NFBG



Main Body		Bolt	
Material	Surface Treatment	Material	Surface Treatment
Polyacetal	Elastomer	SWCH	Trivalent Chromate

Part Number	M (Coarse)	A	Body Color	E	d	t	ℓ	Allowable Load (kN)	Mass (g)	Unit Price
Type	D									
NFBG	32	6	25	B (Black) W (White)	16.5	27	5	0.8	18	
		8	30				6.5	29		
	40	8	30			7.8	35	51		
		10	32							

Ordering Example: Part Number - M - A - Body Color
NFBG32 - 6 - 25 - W

Specification



Tensile Test (Reference)


NFBG	Existing NFB
6kg	2kg

Three times less slippery than the existing NFB type.

Test Conditions


- Desk (Steel Top Plate)
- 4 pcs. used for 9.5kg load
- The force it starts slipping with is measured with a Push-Pull Gauge.

Separate Type / Knurled Type



RoHS 10


KFB (Separate Type)



Ⓢ Separable threads and pad are convenient for disposal.

KFBR (Knurled Type)

D=40A, 50A, 60 D=40B, 50B



Type	Main Body	Bottom	Bolt	Surface Treatment
KFB	ABS Resin	-	-	Trivalent Chromate
KFBR	Polyamide	Polyurethane	SWRM	Trivalent Chromate

Part Number	M (Coarse)	A	ℓ	E	Allowable Load (kN)	Mass (g)	Unit Price
Type	D						
KFB	40	8	25	2	0.28	24	
	50	10		3		28	
	60	12		15		30	
KFBR	40A	8	24	-	0.78	35	
	40B	8	32			54	71
	50A	10	25.5			24	58
	50B	10	32			54	114
	60	10	26			24	68

Ordering Example: Part Number - M - A
KFBR50 - 10 - 25