


# Joint Links, Offset Links

**Features:** Joint Links to connect chains. Available in each piece qty. for stocks and repair. Applicable Chains P.1591 Values in ( ) are dimensions of lubrication-free type.

**Joint Link**




**JNTC**  
(Steel)  
**JMTC**  
(Lubrication-Free)  
**JNTS**  
(Stainless Steel)

RoHS10

Part Number	Type	Nominal	h	m	n	t	ØD	H	Unit Price		
									JNTC	JMTC	JNTS
11			2.28	3.17	5.44	0.38	1.57	3.5	-	-	-
15			2.85	3.90	6.75	0.57	1.62	3.7	-	-	-
25			3.80	4.80	8.80	0.78	2.31	5.2	-	-	-
35			5.70	7.10	12.85	1.20	3.60	7.7	-	-	-
40	JNTC (Steel)	8.02(8.65)	9.53(10.20)	17.55(18.85)	1.15(1.5)	3.97(3.96)		11.7(10.4)			
50	JMTC (Lubrication-Free)	10.15(10.60)	11.60(12.70)	21.75(23.30)	2.00	5.09(5.08)		14.6(13.0)			
60	JNTS (Stainless Steel)	12.65(13.55)	14.15(15.50)	26.80(29.05)	2.40	5.96(5.95)		17.5(15.3)			
80			16.07	19.18	35.00	3.20	7.94	21.1	-	-	-

**Offset Link**



**JNOC**  
(Steel)  
**JMOC**  
(Lubrication-Free)  
**JNOS**  
(Stainless Steel)


\* Use offset links when an odd number of links are required.

Values in ( ) are dimensions of lubrication-free type.

Part Number	Type	Nominal	h	m	n	t	ØD	H	W	Unit Price		
										JNOC	JMOC	JNOS
35			5.70	7.10	12.80	1.25	3.59	8.8	4.78	-	-	
40			8.02(8.20)	9.53(11.30)	17.55(20.50)	1.50(2.00)	3.97(3.96)	11.7(12.0)	7.95(7.55)			
50			10.15(10.90)	11.60(13.20)	21.75(24.10)	2.00(2.40)	5.09(5.08)	14.6(15.0)	9.53(9.26)			
60			12.65(14.50)	14.15(17.00)	26.80(31.50)	2.40(3.20)	5.96(5.95)	17.5(18.0)	12.70(12.20)			
80			16.07	19.18	35.25	3.20	7.94	23.0	15.88	-	-	

**Features:** Joint Links made of standard chains with attachment. Applicable chains P.1592

**Chains with Attachments Joint Link**



**JNT-L**      **JNT-T**

Material: Steel


Part Number	Type	Nominal	Pin		Plate		Attachment				Unit Price	
			L <sub>1</sub>	L <sub>2</sub>	t	C	X	Y	N	d	JNT-L	JNT-T
40	JNT-L (One Side Type)	8.07	9.48	1.5	8.5	12.7	17.4	9.5	3.6			
50	JNT-L	10.17	11.63	2.0	10.5	15.9	22.3	12.7	5.2			
60	JNT-T	12.70	14.20	2.4	12.2	19.05	27.2	15.9	5.2			
80	JNT-T (Both Sides Type)	16.15	19.25	3.2	15.88	25.4	35.2	19.1	6.8			

When ordering 1~ 9 link(s), "Unit Price + Low Quantity Surcharge (Line Item)" is applied.

Ordering Example **Part Number**  
JNTC60  
JNT-L40

**Features:** Joint Links for double Pitch Chains. Applicable Chains P.1591

**Double Pitch S Type Dedicated Joint Link**



**JNTWC**

Material: Steel

Part Number	Type	Nominal	h	m	n	T	t	ØD	ØR	H	W
	50	10.15	11.60	21.75	2.0	2.0	5.09	10.16	14.6	9.53	

Part Number	Unit Price		Volume Discount Rate
	Type	Nominal	
JNTWC	40	1 ~ 20 Link(s)	21 ~ 50 Links
	50		

Ordering Example **Part Number**  
JNTWC40

For orders larger than indicated quantity, please request a quotation.