


# Offset Pull Handles



**Standard**

RoHS10

Type		Material	Surface Treatment
No Washer	With Washer		
UHFN	UHFNZ	SS400	Chrome Plating
UHFNS	UHFNSZ	SUS304	Buffing
UHFNA	UHFNAZ	Aluminum Alloy	Buffing
UHFNEA	UHFNEAZ		Clear Anodize
UHFNB	UHFNBZ		Electrostatic Paint (Mat Black)

• For washers sold separately, refer to P.1180.

**No Washer**

**With Washer**

**No Washer**

Part Number Type	L	L1	Allowable Load (N)	Reference Mass (g)	Unit Price				
					UHFN	UHFNS	UHFNA	UHFNEA	UHFNB
<b>UHFN</b> (Steel) <b>UHFNS</b> (Stainless Steel) <b>UHFNA</b> (Aluminum) <b>UHFNEA</b> (Aluminum) <b>UHFNB</b> (Aluminum, Black)	48	58	2000	90					
	66	76		100					
	88	98		114					
	100	110		122					
	110	120		127					
	120	130		134					
	125	135		136					
	160	170		158					

**With Washer**

Part Number Type	L	Washer Selection	L1	Allowable Load (N)	Reference Mass (g)	Unit Price				
						UHFNZ	UHFNSZ	UHFNAZ	UHFNEAZ	UHFNBZ
<b>UHFNZ</b> (Steel) <b>UHFNSZ</b> (Stainless Steel) <b>UHFNAZ</b> (Aluminum) <b>UHFNEAZ</b> (Aluminum) <b>UHFNBZ</b> (Aluminum, Black)	48	G (SUM22L + Chrome Plating)	58	2000	90					
	66		76		100					
	88		98		114					
	100		110		122					
	110	B (SUM22L + Electrostatic Paint (Black))	120		127					
	120		130		134					
	125		135		136					
	160		S (SUS304)		170	158				

Ordering Example: **Part Number** - **Washer Selection**  
**UHFN66** - **G**  
**UHFNZ100** - **G**

**Small Diameter**

RoHS10

**UHFNSC**

Material	Surface Treatment
SUS304	Buffing

Part Number Type	L	D	H	A	d	M	Allowable Load (N)	Reference Mass (g)	Unit Price 1 - 9 pc (s)	Volume Discount Rate		
										10~49	50~99	100~200
UHFNSC	60	6	30	16	7	4	392	23				
	80		31.5									
	100	8	32	18	10	5		490	54			
	120		40									

Ordering Example: **Part Number**  
**UHFNSC80**