


Oval / Square Bar Pull Handles



Oval Bar Type

RoHS 10

Type	Material	Surface Treatment
① UABL	Aluminum Alloy	Tumble Polish
② UABR		Electrostatic Paint (Mat Black)
③ UABLA		Buffing
④ UABLC	SUM22L or SUM24L	Chrome Plating
⑤ UABS	SUS304	Sandblasting

Part Number Type	A	L	L1	Lf	H	h	M (Coarse)	Allowable Load (N)	Unit Price				
									UABL	UABR	UABLA	UABLC	UABS
UABL (Tumble Polish) UABR (Electrostatic Paint) UABLA (Buffing) UABLC (Steel) UABS (Stainless Steel)	20	100	113	10	47	34	M6	1100					
		112	125					700					
		120	133					600					
		128	141					470					
		160	173					2300					
		112	129					1400					
	26	120	137	12	53	36	M8	1200					
		128	145					600					
		160	177					500					
		180	197					470					
		192	209					380					
		300	317					300					

Ordering Example: Part Number **UABL20** - L **100**

Square Bar Pull Handles - L Fixed

RoHS 10

Type	Material	Surface Treatment
① USAN	SS400	Chrome Plating
② USANS	SUS304	Buffing
③ USANA	Aluminum Alloy	Buffing
④ USANB	Aluminum Alloy	Electrostatic Paint (Mat Black)

Part Number Type	L	L1	Allowable Load (N)	Reference Mass (g)	Unit Price			
					USAN	USANS	USANA	USANB
USAN (Steel) USANS (Stainless Steel) USANA (Aluminum) USANB (Aluminum, Black)	80	88	2500	76				
	100	108		88				
	125	133		103				
	160	168		125				
	200	208		150				
	250	258		180				

Ordering Example: Part Number **USAN80**

U-Shaped Square Bar

RoHS 10

USANK

Material	Surface Treatment
Zinc Alloy	Chrome Plating

Part Number Type	L	L1	W	H	B	S	M (Coarse)	Reference Mass (g)	Unit Price
100	108	14	30	8	8	M5	80		
110	120	16	40	10	8	M6	130		
120	130	16	40	10	8	M6	145		
188	200	18	50	12	10	M8	250		

Ordering Example: Part Number **USANK100**

Square Bar Pull Handles - L Configurable

RoHS 10

Type	Material	Surface Treatment
USANSF	SUS304	Buffing

Part Number Type	L 1mm Increment	Allowable Load (N)	Unit Price
USANSF	80~125	2500	
	126~250		
	251~300		

Ordering Example: Part Number **USANSF** - L **85**