

Hydraulic Fittings


Straight

PT/PT, Male Threads Straight



RoHS 10

Type	Material	Surface Treatment
YCPT	S35C	Trivalent Chromate
YCPTS	SUS304	-



Part Number	Type	No.	T1 R (PT)	T2 R (PT)	L	l1	l2	B	Unit Price	
									YCPT	YCPTS
11		1/8	1/8	26	10	10	12			
12		1/8	1/4	31	10	13	17			
13		1/8	3/8	33	10	15	21			
22		1/4	1/4	34	13	13	17			
23		1/4	3/8	36	13	15	21			
33		3/8	3/8	37	15	15	21			
34		3/8	1/2	40 (46)	14 (16)	17 (19)	26 (22)			
44		1/2	1/2	43	17	17	26 (22)			
46		1/2	3/4	46 (48)	17 (18)	19	32 (27)			
66		3/4	3/4	48	19	19	32 (27)			


YCPT
YCPTS
Dimension in ()
are for YCPTS.

PT/PF, Male Threads Straight Male



RoHS 10

Type	Material	Surface Treatment
YCPFP	S35C	Trivalent Chromate
YCPFPS	SUS304	-



Part Number	Type	No.	T R (PT)	F G (PF)	L	l1	l2	B	Unit Price	
									YCPFP	YCPFPS
11F		1/8	1/8	31	10	13	14			
12F		1/8	1/4	34	10	16	19			
13F		1/8	3/8	37	10	17.5	22			
21F		1/4	1/8	34	13	13	14			
22F		1/4	1/4	37	13	16	19			
23F		1/4	3/8	38.5	13	17.5	22			
31F		3/8	1/8	37	15	13	19			
32F		3/8	1/4	38.5	15	16	19			
33F		3/8	3/8	40.5	15	17.5	22			
34F		3/8	1/2	45	15	20	27			
44F		1/2	1/2	48	18	20	27			
46F		1/2	3/4	52	18	22	32			
64F		3/4	1/2	50	20	20	27			
66F		3/4	3/4	54	20	22	36			


YCPFP
YCPFPS

PT Male Threads / PF Female Threads Straight Female



RoHS 10

Type	Material	Surface Treatment
YCPFGP	S35C	Trivalent Chromate




Part Number	Type	No.	T R (PT)	F G (PF)	L	l1	l2	B	Unit Price	
									YCPFGP	
22F		1/4	1/4	38	13	8	19			
33F		3/8	3/8	42	15	8	22			
44F		1/2	1/2	50	18	10	27			

PT Female Threads / PF Female Threads Straight Male



RoHS 10

Type	Material	Surface Treatment
YCPFFP	S35C	Trivalent Chromate
YCPFFSP	SUS304	-




Part Number	Type	No.	T Rc (PT)	F G (PF)	L	l1	B	Unit Price	
								YCPFFP	YCPFFSP
22F		1/4	1/4	33	16	19			
33F		3/8	3/8	37	18	22			
44F		1/2	1/2	42	20	27			




Specifications Applicable Fluids : Oil, Water
Max. Operating Pressure : 20.6MPa (210kgf/cm² or less)

PT/PF, Male Threads Straight Female



RoHS 10

Type	Material	Surface Treatment
YCPF	S35C	Trivalent Chromate
YCPFSS	SUS304	-



Part Number	Type	No.	T R (PT)	F G (PF)	L	l1	l2	B	Unit Price	
									YCPF	YCPFSS
11F		1/8	1/8	27	10	11	14			
12F		1/8	1/4	32	10	13	19			
13F		1/8	3/8	34	10	15	22			
21F		1/4	1/8	32	13	11	14			
22F		1/4	1/4	34	13	13	19			
23F		1/4	3/8	36	13	15	22			
31F		3/8	1/8	34	15	11	19			
32F		3/8	1/4	36	15	13	19			
33F		3/8	3/8	38	15	15	22			
34F		3/8	1/2	42	15	17	27			
44F		1/2	1/2	47	18	18	27			
46F		1/2	3/4	50	18	20	32			
64F		3/4	1/2	47	20	17	27			
66F		3/4	3/4	53	20	20	36			


YCPF
YCPFSS

PT Male Threads / PF Female Threads Straight Male



RoHS 10


Type	Material	Surface Treatment
YCPFG	S35C	Trivalent Chromate
YCPFGS	SUS304	-



Part Number	Type	No.	T R (PT)	F G (PF)	L	l1	l2	B	Unit Price	
									YCPFG	YCPFGS
11F		1/8	1/8	31	10	6	14			
12F		1/8	1/4	34	10	8	19			
21F		1/4	1/8	34	13	6	14			
22F		1/4	1/4	38	13	8	19			
23F		1/4	3/8	39	13	8	22			
32F		3/8	1/4	39	15	8	19			
33F		3/8	3/8	42	15	8	22			


YCPFG
YCPFGS

PT Female Threads / PF Female Threads Straight Female



RoHS 10

Type	Material	Surface Treatment
YCPFF	S35C	Trivalent Chromate
YCPFFS	SUS304	-




Part Number	Type	No.	T Rc (PT)	F G (PF)	L	l1	B	Unit Price	
								YCPFF	YCPFFS
22F		1/4	1/4	30	13	19			
33F		3/8	3/8	34	15	22			
44F		1/2	1/2	40	18	27			

PT/PF, Male Threads Long Straight Female



RoHS 10

Type	Material	Surface Treatment
YCLPF	S35C	Trivalent Chromate



Part Number	Type	No.	T R (PT)	F G (PF)	L	l1	B	Unit Price	
								YCLPF	
22F		1/4	1/4	75	13	19			
33F		3/8	3/8	78	15	22			
44F		1/2	1/2	93	18	27			



Ordering Example Part Number
YCPT11