



Long Nuts for Aluminum Extrusions

For 5 Series (Slot Width 6mm)




Tightening Torque **P526**




Type		Material	Surface Treatment	Reference Tightening Torque (N · m)
Pre-Assembly	Post-Assembly	S10C Equivalent	Trivalent Chromate	
HNTLF5	HNTALF5			
HNTLP5	HNTALP5			
HNTLS5	HNTALS5	SUS303 Equivalent	-	
SHNTLF5	-			
SHNTLP5	SHNTALP5			
SHNTLS5	SHNTALS5			

Cross Section Shape	A	B	E	T
Pre-Assembly	5.8	10	3.5	4.1
Post-Assembly	5.8	8	2.5	3.2



Reference Tightening Torque (N · m)	
M	S10C Equivalent, SUS303 Equivalent
5	6.8



No Hole Type

Part Number	L 1mm Increment	HNTLF5		SHNTLF5		HNTALF5	
		Unit Price (Less than 300mm)	Unit Price / m (300mm or More)	Unit Price (Less than 300mm)	Unit Price / m (300mm or More)	Unit Price (Less than 300mm)	Unit Price / m (300mm or More)
(Pre-Assembly Insertion) HNTLF5	(Post-Assembly Insertion) HNTALF5	(Pre-Assembly Insertion) 50-2000	(Post-Assembly Insertion) 50-1000				
SHNTLF5							

Pitch Configurable Type

Part Number	L 1mm Increment	M	N 1mm Increment	P 1mm Increment	Number of Taps S	HNTLP5		SHNTLP5		HNTALP5		SHNTALP5	
						Unit Price (Less than 300mm)	Unit Price / m (300mm or more)	Unit Price (Less than 300mm)	Unit Price / m (300mm or more)	Unit Price (Less than 300mm)	Unit Price / m (300mm or more)	Unit Price (Less than 300mm)	Unit Price / m (300mm or more)
(Pre-Assembly Insertion) HNTLP5	(Post-Assembly Insertion) HNTALP5	(Pre-Assembly Insertion) 50-2000	(Post-Assembly Insertion) 50-1000	3 4 5	5 ≤ N ≤ L-5	2M ≤ P ≤ L-2M	2 ≤ S ≤ 20						
SHNTLP5													

Hole Position Configurable Type

Part Number	L 1mm Increment	M	XA ~ XE 1mm Increment	HNTLS5		SHNTLS5		HNTALS5		SHNTALS5	
				Unit Price (Less than 300mm)	Unit Price / m (300mm or More)	Unit Price (Less than 300mm)	Unit Price / m (300mm or More)	Unit Price (Less than 300mm)	Unit Price / m (300mm or More)	Unit Price (Less than 300mm)	Unit Price / m (300mm or More)
(Pre-Assembly Insertion) HNTLS5	(Post-Assembly Insertion) HNTALS5	(Pre-Assembly Insertion) 50-2000	(Post-Assembly Insertion) 50-1000	3 4 5	5-L-5						
SHNTLS5											


Number of tapped holes can be specified between 1 to 5.




- Part Number - L
- HNTLF5 - 1800
 - HNTALF5 - 400
- Part Number - L - M - N - P - S
- HNTLP5 - 200 - M3 - N10 - P30 - 7
 - HNTALP5 - 210 - M5 - N8 - P15 - 8
- Part Number - L - M - XA - XB - XC - XD - XE
- HNTLS5 - 1050 - M5 - XA20 - XB105
 - SHNTLS5 - 1050 - M5 - XA20 - XB105 - XC250 - XD500 - XE755
 - HNTALS5 - 1000 - M5 - XA25 - XB55 - XC78 - XD975 - XE992

Hole Machining Charge

Pitch Configurable Type	Unit Price / Hole	Hole Position Configurable Type	Unit Price / Hole
HNTLP5, HNTALP5		HNTALP5, HNTALP5	
SHNTLP5, SHNTALP5		SHNTLP5, SHNTALP5	



Long Nuts L Dimension Fixed Type



Reference Tightening Torque (N · m)	
M	S10C Equivalent, SUS303 Equivalent
5	6.8

Type	Material	Surface Treatment
HNTK5	S10C Equivalent	Trivalent Chromate
HNTLG5	SUS303 Equivalent	-
SHNTLG5	SUS303 Equivalent	-

L Dimension Fixed without Holes

Part Number	Unit Price	Volume Discount Rate
HNTK5	1 ~ 499 pc(s)	500-999 1000-1500

Ordering Example: Part Number HNTLG5

Alterations: Part Number - (SET) HNTLG5 - SET

L Dimension Fixed with Holes

Part Number	Unit Price	Volume Discount Rate
HNTLG5	1 ~ 499 pc(s)	500-999 1000-1500
SHNTLG5 (Stainless Steel)		

Alteration	Code	Spec.	Type
Hex Socket Set Screw Set	SET	Hex socket set screws come as a set.	HNTLG5
		Type	Set Screw Quantity
		HNTLG MSSK 4	SHNTLG MSSU 4
			SHNTLG5