



# One-Touch Couplings for Clean Applications

**Connectors**



**PPCN**




**RoHS 10**


**M** Material: Polypropylene

Part Number Type	D	Nominal	A	B	L	Width Across H	Thread Size M	Effective Sectional Area (mm <sup>2</sup> )	Mass (g)	Unit Price 1 - 9 pcs(s)	Volume Discount Rate 10-30	
PPCN	4	1	8	21.1	17.1	12	R1 / 8	3.4	2.5			
		2	8	22.8	18.8	14	R1 / 8	9.1	3			
	6	1	11	24.8			R1 / 4		3.5			
		2	8	27.9	23.9		R1 / 8			4.5		
	8	2	11	26.6	20.6		R1 / 4	22.1				
		3	12	27.5	21.2		R3 / 8			6		
	10	2	11	32.6	26.6		R1 / 4	30.5		7		
		3	12	33.6	27.3		R3 / 8			8		
	12	3	12	37.6	31.3	22	R3 / 8	40.7	12			

**Elbows**



**PPCNL**




**RoHS 10**


**M** Material: Polypropylene

Part Number Type	D	Nominal	A	B	L	P	E	Width Across H	Thread Size M	Effective Sectional Area (mm <sup>2</sup> )	Mass (g)	Unit Price 1 - 9 pcs(s)	Volume Discount Rate 10-30	
PPCNL	4	1	8	23.3	24.3	10	18.1	10	R1 / 8	3.4	4			
		2	8	25	27.3	12.5	19.9	12	R1 / 8	8.7	5			
	6	1	11	28	28.2				14	R1 / 4		5.5		
		2	8	28	31.3	14.5	22.7		14	R1 / 4	17.2	7.5		
	8	2	11	31	32.2				17	R3 / 8		8.5		
		3	12	32.8	33.7				17	R1 / 4	25.9	12		
	10	2	11	36	38.7	17.5	26.4		17	R3 / 8		13		
		3	12	37	39.4				22	R3 / 8	37.6	18		
	12	3	12	39	43.2	21	29.6	22	R3 / 8					

**Union Straight**



**PPCR**




**RoHS 10**


**M** Material: Polypropylene

Part Number Type	D	B	P	Mass (g)	Effective Sectional Area (mm <sup>2</sup> )	Unit Price 1 - 9 pcs(s)	Volume Discount Rate 10-30
PPCR	4	31	10	4	5.3		
	6	35.2	12.5	5.5	12.5		
	8	37.8	14.5	8	20		
	10	43.8	17.5	13	35		
	12	48.2	21	19	59		

**Union Elbows**



**PPCL**




**RoHS 10**


**M** Material: Polypropylene

Part Number Type	D	B	P	E	d	F	Mass (g)	Effective Sectional Area (mm <sup>2</sup> )	Unit Price 1 - 9 pcs(s)	Volume Discount Rate 10-30
PPCL	4	22	10	17	3.2	6.5	4.5	4.2		
	6	26.5	12.5	20.2	3.2	8	6	10		
	8	30	15	22.4	4.2	10	9	16.5		
	10	35.2	17.5	26.4	4.2	12	14	30		
	12	40.1	21	29.6	4.2	14	20	47		

**Union Tees**



**PPCE**




**RoHS 10**


**M** Material: Polypropylene

Part Number Type	D	P	E	d	F	G	Mass (g)	Effective Sectional Area (mm <sup>2</sup> )	Unit Price 1 - 9 pcs(s)	Volume Discount Rate 10-30
PPCE	4	10	17	3.2	6.5	13	6.5	5.3		
	6	13	20.2	3.5	8	16	9	12.5		
	8	15	22.2	3.5	9	18	13	20		
	10	17.5	25.4	4.2	12	24	21	35		
	12	21	28.6	4.2	14	28	30	59		

**Union Y**



**PPCY**




**RoHS 10**


**M** Material: Polypropylene

Part Number Type	D	B	P	J	d	F	Mass (g)	Effective Sectional Area (mm <sup>2</sup> )	Unit Price 1 - 9 pcs(s)	Volume Discount Rate 10-30
PPCY	4	33	10	11	3.4	14.2	6.5	4.2		
	6	38	13	12	3.4	15.9	9	10		
	8	42.4	15	14	3.4	17.2	13	16.5		
	10	48.8	18	18	4.5	19.7	22	27		
	12	55.2	21.5	20	4.2	22.4	31	38		

**Reducers**



**PPCGY**




**RoHS 10**


**M** Material: Polypropylene

Part Number Type	D1	D2	B	L	P	Mass (g)	Effective Sectional Area (mm <sup>2</sup> )	Unit Price 1 - 9 pcs(s)	Volume Discount Rate 10-30
PPCGY	6	4	37.8	15.3	10	3.5	5.3		
		4	40.3	16.8		4	5.3		
	8	6	40.9	17.4	12.5	4.5	9		
		6	43.9	18.9	12.5	5.5	9		
	10	8	43.7	18.7	14.5	6.5	20		
		8	49.7	20.7	14.5	8.5	20		
	12	10	50.2	21.2	17.5	10	35		

**Panel Mount**



**PPMP**



**RoHS 10**

**M** Material: Body: Polypropylene  
Metal Part: SUS304

Part Number Type	D	B	E	A	P	C	H	G	Thread Size M	Mass (g)	Effective Sectional Area (mm <sup>2</sup> )	Unit Price 1 - 9 pcs(s)	Volume Discount Rate 10-30	
PPMP	4	31.6	9.3	12	10	15	14	5	M12x1.5	7.2	4.2			
	6	35.8	9.9	15	12.3	17.1	17	5	M14x1.5	10.2	10.7			
	8	38.4	10.7	15.5	14.2	18.4	19	6	M16x1.5	14.3	19.1			
	10	43.4	13.2	18.5	17.5	20.9	24	6	M20x1.5	24.4	39.6			
	12	8	38.8	13.4	20.5	21	23.6	27	6	M24x1.5	30.4	47.6		