


# Dimension Selectable Plates - Aluminum

A5052P (Al-Mg Aluminum Alloy)




4-Surface Milled (Rolled)



RoHS10

ALNH



Ordering Example

Part Number - A - B - T  
 Example ALNH - 350 - 200 - 10

### Precision Standards

- Flatness 1.5 or Less per 1000mm
- T Dimension Tolerance
 

	5	6	8	10	12, 15	20	25	30
	±0.35	±0.45	±0.5	±0.6	±0.7	±0.8	±0.9	±1.0
- A, B Dimension Tolerance
 

	25~100	101~250	251~500
	±0.2	±0.25	±0.4
- Perpendicularity of Datum Plane 0.015 or less per 100mm
- Circumference Chamfering C0.3 or Less

Part Number	A	T												
		B	5	6	8	10	12	15	20	25	30			
	100	100												
	125													
	150													
	160													
	200													
	250													
	300													
	350													
	400													
	450													
	500													
	125	125												
	150													
	160													
	200													
	250													
	300													
	350													
	400													
	450													
	500													
	150	150												
	160													
	200													
	250													
	300													
	350													
	400													
	450													
	500													
	160		160											
	200													
	250													
	300													
	350													
	400													
	450													
	500													
	200	200												
	250													
	300													
	350													
	400													
	450													
	500													
	250		250											
	300													
	350													
	400													
	450													
	500													
	300	300												
	350													
	400													
	450													
	500													

ALNH  
(Standard Size)