


# Dust Collection Nozzles



RoHS 10

Type	Material	Heat Resistance Temp.
SJNZJ	PE	70°C

■ **Features:** Dust Collection Nozzles intended to collect dusts as the final step, after dust removal is done by using the other nozzle.  
 : Can also be used to discharge dusts.  
 : Have the Antistatic property and thus, can be used in a wide range of environments.



Part Number		D	A	B	L	Unit Price 1 ~ 4 pc(s).	Volume Discount Rate		
Type	No.						5~39	40~99	100~200
SJNZJ	1	50	70	120	120				
	2		70	200	150				
	3	65	100	200	170				


For orders larger than indicated quantity, please check with WOS.




Ordering  
Example

Part Number  
SJNZJ1

■ Differential Pressure Characteristic Table : Suction



■ Differential Pressure Characteristic Table : Discharge



■ Dust Collection Nozzle Measurement Position

8	2	5
7	1	4
9	3	6



Alterations



Part Number - (KFJ, KLB)  
SJNZJ1 - KFJ



Example

Alterations	Adds Flange	Adds L-Shaped Bracket																			
Code	KFJ	KLB																			
Spec.	Machines a flange to fix the current nozzle. The resulting flange is secured through the Riveting method. [Ordering Code] KFJ 🔴 The product will be shipped on the 3rd day after the order is received.	Mounts an L-Shaped Bracket to fix the current nozzle. The resulting bracket is secured through the Riveting method. [Ordering Code] KLB 🔴 The product will be shipped on the 3rd day after the order is received.																			
	<table><tr><th>Part Number</th><th>D1</th><th>P.C.D</th><th>D</th><th>d</th></tr><tr><td>SJNZJ1</td><td>80</td><td>70</td><td>56.2</td><td>50.2</td></tr><tr><td>SJNZJ2</td><td></td><td></td><td></td><td></td></tr><tr><td>SJNZJ3</td><td>100</td><td>90</td><td>71.2</td><td>65.2</td></tr></table>	Part Number	D1	P.C.D	D	d	SJNZJ1	80	70	56.2	50.2	SJNZJ2					SJNZJ3	100	90	71.2	65.2
Part Number	D1	P.C.D	D	d																	
SJNZJ1	80	70	56.2	50.2																	
SJNZJ2																					
SJNZJ3	100	90	71.2	65.2																	

